

Material	152507P
Material description	Methanol
Grade	HiPerSolv CHROMANORM for HPLC
CAS Number	67-56-1
Molecular formula	CH ₄ O
Molecular mass	32.04

Characteristics	Specifications
Assay	≥ 99.8 %
Acidity	≤ 0.00007 meq/g
Alkalinity	≤ 0.0001 meq/g
Density (20/4)	0.7900 - 0.7920
Non-volatile residue	≤ 5 ppm
Water	≤ 0.0500 %
Transmittance (210 nm)	≥ 60.0 %
Transmittance (220 nm)	≥ 80.0 %
Transmittance (230 nm)	≥ 90.0 %
Transmittance (235 nm)	≥ 92.0 %
Transmittance (240 nm)	≥ 95.0 %
Transmittance (250 nm)	≥ 98.0 %
Transmittance (260 nm)	≥ 98.0 %

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

VWR International

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.