



Material	23223.290
Material description	Cyclohexane
Grade	GPR RECTAPUR
CAS Number	110-82-7
Molecular formula	C <sub>6</sub> H <sub>12</sub>
Molecular mass	84.16

Characteristics	Specifications
Assay	Min. 99.0 %
IR Spectrum	Passes test
Substances coloured by H <sub>2</sub> SO <sub>4</sub>	Passes test
Boiling point	79 --> 81 °C
Density (20/4)	0.778 --> 0.779
Free acidity	Max. 0.0002 meq/g
Solidification point	5.5 --> 6.5 °C
Evaporation residue	Max. 50 ppm

## Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare  
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;  
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.