



Material	20858.550
Material description	Propan-1-ol
Grade	GPR RECTAPUR
CAS Number	71-23-8
Molecular formula	C ₃ H ₈ O
Molecular mass	60.10

Characteristics	Specifications
Assay	Min. 99 %
IR Spectrum	Passes test
Acidity	Max. 0.002 meq/g
Boiling point	96.3 --> 97.5 °C
Density (20/4)	0.801 --> 0.804
Substances coloured by H ₂ SO ₄	Max. 150 APHA
Evaporation residue	Max. 100 ppm
Methanol	Max. 0.1 %
Water	Max. 0.2 %

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.