



Model:

**SZB350 OH - 630-1583**

Typology:

**LABORATORY STEREOMICROSCOPE**

Description:

*Stereomicroscope for laboratory and industry applications.*

<b>Illumination</b>	The microscope is not equipped with its own illumination, but it can use external illumination systems (halogen, LED, fiber guides).
<b>Focusing</b>	By means of a rack and pinion controlled by a pair of knobs placed on both sides of the stereomicroscope..
<b>Stand</b>	Overhanging stand, pillar height 42 cm. Horizontal arm 45 cm. Base: 23x23x6h cm. Weight: 15 Kg
<b>Head</b>	Binocular rotating 360° and 45° inclined. Diopter adjustment on both eyepieces. Interpupillary adjustment 51-75 mm.
<b>Eyepieces</b>	Widefield eyepieces WF10x/20 with field number 20.
<b>Objectives</b>	Parfocal achromatic objective 1X Working distance: 100 mm Zoom range: 0,7x - 4,5x Zoom factor: 6,428:1
<b>Accessories</b>	Instruction manual and dust cover included.