



SMZ140 N2GG

Model SMZ140 N2GG

Optical System Greenough

Observation Tube Binocular head

Interpupillary distance 54-76mm

Diopter adjustment On both tubes , +/- 5 diopter

Inclination 45° inclined, 360° rotating

Eyepieces WF10X/20mm

Objectives system Zoom, ratio1:4

Objectives magnification 1X~4X

Working distance 80mm

Stand Pole type stand with transmitted illumination

Base 237x170mm

Column/Arm Ø25mm, 210mm high

Head holder For Ø25mm column and Ø74mm head with incident illumination

Focus mechanism Coarse focusing system with tension adjustment

Focusing stoke 49mm

Incident illumination Halogen 12V/15W with intensity control

Transmitted illumination Halogen 12V/10W with intensity control

Transformer Internal **Power supply** 220V

Accessories included Black, white and frosted stage plates and dust cover

Length x Width x Height 237x170x335mm

Weight 6,2Kg



Add a Moticam camera to capture, document, annotate and share images and videos with the Motic Images Plus software.