



Material	443922U
Material description	Ethidium bromide 10 mg/ml in aqueous solution
Grade	Electran

Characteristics	Specifications
Identity (UV/VIS-Spectrum)	passes test
Absorption maximum (water)	478 - 482 nm
Spec. Absorptivity A 1%/1cm (I^0m^{ax} ; 0.0	140 - 160
Suitability for electrophoresis	passes test

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

VWR International