

Novobiocin MKTTn supplement**Code 84722.0001****Intended use**

Freeze-dried selective supplement for the preparation of MKTTn broth used for the enrichment procedure for detection of *Salmonella* spp. in food and animal feeding stuffs (ISO 6579).

Vial contents

Novobiocin20.0 mg

Instructions for preparation

Aseptically reconstitute the contents of one vial with 5 ml of sterile purified water. Mix well and aseptically add to 500 ml of Muller-Kauffmann tetrathionate-novobiocin broth (MKTTn) (ISO) (Art. N°: 84624.0500) autoclaved and cooled to approximately 45-50 °C. Add also 10 ml of Iodine-iodide solution (Art. N° 84723.0001). Mix well and pour into sterile tubes or flasks under aseptic conditions.

Instructions for use

For laboratory use only.

Consult the technical sheet of Muller-Kauffmann tetrathionate-novobiocin broth (MKTTn) (ISO) (Art. N°: 84624.0500)

Consult the material safety data sheet before the use.

Physical characteristics

Appearance of freeze-dried supplement	Short, dense, white pellet
Appearance of solution after reconstitution	Colourless, limpid
pH of complete medium (25°C)	8.0 ± 0.2

Storage conditions

Store at 2-8°C. When stored as directed the supplement remains stable until the expiry date shown on the label. Do not use beyond stated expiry date.

Ordering information

84722.0001	Novobiocin MKTTn supplement	10 vials, each for 500 ml of complete medium
------------	-----------------------------	--