

Datasheet

HA polyclonal antibody (HRP)

Catalog Number: PAB29059

Regulation Status: For research use only (RUO)

Product Description: Chicken polyclonal antibody raised against recombinant HA peptide.

Immunogen: A KLH-conjugated synthetic peptide corresponding to HA tag emulsified in Freund's adjuvant.

Sequence: YPYDVPDYA

Host: Chicken

Applications: WB

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Conjugation: HRP

Purification: Antigen affinity purification

Isotype: IgY

Recommend Usage: Western Blot(1:5000)

The optimal working dilution should be determined by the end user.

Storage Buffer: In 50mM HEPES, pH 7.0, 0.1M NaCl, (0.2% BSA, 0.01% thimerosal).

Storage Instruction: Store at 4°C and avoid from light.

For long term storage, dilute the antibody with sterile glycerol and store it at -20°C.

Aliquot to avoid repeated freezing and thawing.