9F, No. 108, Jhouzih St., Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

MYO9A monoclonal antibody (M04), clone 4C11

Catalog Number: H00004649-M04

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a partial recombinant MYO9A.

Clone Name: 4C11

Immunogen: MYO9A (NP_008832, 719 a.a. ~ 828 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:
GKRNIHRKTGHDDTAPCAILKSMDSFSFLQHPVHQRS
LEILQRCKEEKYSITRKNPRTPLSDLQGMNALNEKNQH
DTFDIAWNGRTGIRQSRLSSGTSLLDKDGIFANST

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Re
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 4649

Gene Symbol: MYO9A

Gene Alias: FLJ11061, FLJ13244, MGC71859