Motic®

MORE THAN MICROSCOPY



K-400 L

Model	K-400 L
Optical System	Common main objective (CMO) Infinity optical system
Observation Tube	Binocular head
Interpupillary distance	54-76mm
Diopter adjustment	On both tubes , +/- 5 diopter
Inclination	45° inclined
Eyepieces	WF10X/23mm
Objectives system	4-position step magnification changer
Standard objective	1X Achromatic
Objectives magnification	6X, 12X, 25X and 50X
Working distance	89mm
Stand	Pole type stand with transmitted illumination
Base	329x277mm
Column/Arm	Ø32mm, 295mm high
Optical body with head holder	For Ø32mm column with incident illumination
Focus mechanism	Coarse focusing system with tension adjustment
Focusing stoke	49mm
Incident illumination	Halogen 12V/10W with intensity control
Transmitted illumination	Halogen 12V/10W with intensity control
Transformer	Internal
Power supply	100-240V (CE)
Accessories included	Black, white and frosted stage plates and dust cover
Length x Width x Height	329x277x434mm
Weight	5,9Kg

GO DIGITAL

Add a Moticam camera to capture, document, annotate and share images and videos with the Motic Images Plus software.

Please verify the local availability of the product with your Motic Representative.