Technical Data Sheet

Chloramphenicol supplement Code 84729.0001

Intended use
Freeze-dried selective supplement for the preparation of yeasts and moulds plating media.

Vial contents
Chloramphenicol……. 50.0 mg

Instructions for preparation
Aseptically reconstitute the contents of one vial of Chloramphenicol supplement with 3 ml of ethanol / sterile purified water (1:1). Mix well and add to the suitable medium base before autoclaving (e.g. 500 ml of DG18 agar base (ISO) Art. N° 84632.0500 or 500 ml of Sabouraud dextrose agar, Art. N° 84633.0500). Sterilise in the autoclave at 121 °C for 15 minutes. Cool to 45-50 °C and distribute into sterile Petri dishes.

Instructions for use
For laboratory use only.
Consult the technical sheet of DG18 agar base (ISO), Art. N° 84632.0500 and/or Sabouraud dextrose agar, Art. N° 84633.0500.
Consult the material safety data sheet before the use.

Physical characteristics

Appearance of freeze-dried supplement	Small, white pastille with needles
Appearance of solution	Colourless, limpid

Storage conditions
Store at 2-8°C. When stored as directed the supplement remains stable until the expiry date shown on the label. Do not use beyond stated expiry date.

Ordering information

84729.0001	Chloramphenicol supplement	10 vials, each for 500 ml of complete medium

VWR International bvba/sprl
Haasrode Research park Zone 3
Geldenaaksebaan 464
b-3001 Leuven Tel +32 (0) 16 385 011

Revision: TS-84729.docx rev 0 - 02-2013