# Safety Data Sheet

*according to Regulation (EC) No. 1907/2006 (amended by Regulation (EU) No 453/2010)*

| *Revision date: 30.07.2014* | *Version: 4.0* | *Print date: 06.08.2014* |
|---|---|---|

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

| | |
|---|---|
| Trade name/designation: | WORT AGAR |
| Product No.: | 84661.0500 (VWR International) |
| Substance name: | |
| CAS No.: | — |
| INDEX No.: | 000-000-00-0 |
| REACH registration No.: | Not yet communicated down the supply chain. |
| Other means of identification: | |

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

| | |
|---|---|
| Relevant identified uses: | General chemical reagent |

### 1.3 Details of the supplier of the safety data sheet

Supplier (manufacturer/importer/only representative/downstream user/distributor)

*United Kingdom*

***VWR International Ltd.***

| | |
|---|---|
| Street | Hunter Boulevard, Magna Park |
| Postal code/city | Lutterworth, LE17 4XN |
| Telephone | 0800 22 33 44 |
| Telefax | 01455 55 85 86 |
| E-mail (competent person) | vwrsds@eu.vwr.com |

**Emergency telephone**

| | |
|---|---|
| Telephone | +44 (0) 1270 502894 |

*Ireland*

***VWR International Ltd.***

| | |
|---|---|
| Street | Orion Business Campus, Northwest Business Park |
| Postal code/city | Ballycoolin, Dublin 15 |
| Telephone | +353 1 8822222 |
| Telefax | +353 1 8822333 |
| E-mail (competent person) | vwrsds@eu.vwr.com |

**Emergency telephone**

| | |
|---|---|
| Telephone | +44 (0) 1270 502894 |

## *Ireland*

### *VWR International (Northern Ireland) Ltd.*

| | |
|---|---|
| Street | Orion Business Campus, Northwest Business Park |
| Postal code/city | Ballycoolin, Dublin 15 |
| Telephone | +353 1 8822222 |
| Telefax | +353 1 8822333 |
| E-mail (competent person) | vwrsds@eu.vwr.com |

**Emergency telephone**

| | |
|---|---|
| Telephone | +44 (0) 1270 502894 |

## *Netherlands*

### *VWR International B.V.*

| | |
|---|---|
| Street | Basisweg 34 |
| Postal code/city | 1043 AP Amsterdam |
| Telephone | +32 16 385 011 |
| Telefax | +32 16 385 385 |
| E-mail (competent person) | vwrsds@eu.vwr.com |

**Emergency telephone**

| | |
|---|---|
| Telephone | +44 (0) 1270 502894 |

## *Switzerland*

### *VWR International GmbH*

| | |
|---|---|
| Street | Lerzenstrasse 16/18 |
| Postal code/city | 8953 Dietikon |
| Telephone | +44 (0) 745 13 13 |
| Telefax | +44 (0) 745 13 10 |
| E-mail (competent person) | vwrsds@eu.vwr.com |

**Emergency telephone**

| | |
|---|---|
| Telephone | 145 |

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

### 2.1.1 Classification according to Regulation (EC) No. 1272/2008 [CLP]

**This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP].**

### 2.2 Label elements

### 2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]

According to EC directives or the corresponding national regulations the product does not have to be labelled.

Other hazards

SVHC No

## SECTION 3: Composition / information on ingredients

### 3.1 Substances

not relevant (Product identifier)

### 3.2 Mixtures

Hazardous ingredients Classification according to Regulation (EC) No. 1272/2008 [CLP]

| Substance name | Concentration | Product identifier | Hazard classes and hazard categories |
|---|---|---|---|
| no data available | | | |

## SECTION 4: First aid measures

### 4.1 General information

When in doubt or if symptoms are observed, get medical advice. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

#### After inhalation

Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration. In case of respiratory tract irritation, consult a physician.

#### In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

#### After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

#### In case of ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

### 4.2 Most important symptoms and effects, both acute and delayed

no data available

### 4.3 Indication of any immediate medical attention and special treatment needed

no data available

### 4.4 Self-protection of the first aider

First aider: Pay attention to self-protection!

### 4.5 Information to physician

no data available

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

**Suitable extinguishing media**

The product itself does not burn. Co-ordinate fire-fighting measures to the fire surroundings.

**Extinguishing media which must not be used for safety reasons**

no restriction

### 5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated: Pyrolysis products, toxic

### 5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives. In case of fire: Wear self-contained breathing apparatus.

### 5.4 Additional information

Do not allow run-off from fire-fighting to enter drains or water courses. Do not inhale explosion and combustion gases. Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen. Use water spray jet to protect personnel and to cool endangered containers.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety. Wear a self-contained breathing apparatus and chemical protective clothing.

### 6.2 Environmental precautions

Do not allow to enter into soil/subsoil. Do not allow to enter into surface water or drains.

### 6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Take up carefully when dry. Avoid generation of dust. Clean contaminated objects and areas thoroughly observing environmental regulations. Collect in closed and suitable containers for disposal.

### 6.4 Additional information

Clear spills immediately.

## SECTION 7: Handling and storage

### 7.1 Precautions for safe handling

Avoid: Inhalation Avoid contact with skin and eyes. Use extractor hood (laboratory). If handled uncovered, arrangements with local exhaust ventilation have to be used. If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means. Protect from moisture.

### 7.2 Conditions for safe storage, including any incompatibilities

storage temperature: 15-25 °C

Storage class: 10-13

Keep container tightly closed in a cool, well-ventilated place.

### 7.3 Specific end use(s)

no data available

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

### 8.2 Exposure controls

**8.2.1 Appropriate engineering controls**

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

**8.2.2 Personal protection equipment**

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn. For the protection against direct skin contact, body protective clothing is essential (in addition to the usual working clothes).

*Eye/face protection*

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

Recommendation: VWR 111-0432

*Skin protection*

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms: DIN EN 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.

By short-term hand contact

| | |
|---|---|
| Suitable material: | NBR (Nitrile rubber) |
| Thickness of the glove material: | 0,12 mm |
| Breakthrough time (maximum wearing time): | > 480 min |
| Recommended glove articles: | VWR 112-0998 |

By long-term hand contact

| | |
|---|---|
| Suitable material: | NBR (Nitrile rubber) |
| Thickness of the glove material: | 0,38 mm |
| Breakthrough time (maximum wearing time): | > 480 min |
| Recommended glove articles: | VWR 112-3717 / 112-1381 |

*Respiratory protection*

Usually no personal respirative protection necessary.Suitable respiratory protection apparatus:

| | |
|---|---|
| Recommendation: | no data available |
| Suitable material: | no data available |
| Recommendation: | no data available |

*Additional information*

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

**8.2.3** *Environmental exposure controls*

no data available

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

| | |
|---|---|
| (a) Appearance | |
| Physical state: | solid |
| Colour: | no data available |
| (b) Odour: | no data available |
| (c) Odour threshold: | no data available |

**Safety relevant basic data**

| | |
|---|---|
| (d) pH: | no data available |
| (e) Melting point/freezing point: | no data available |
| (f) Initial boiling point and boiling range: | no data available |
| (g) Flash point: | no data available |
| (h) Evaporation rate: | no data available |
| (i) Flammability (solid, gas): | not applicable |
| (j) Upper/lower flammability or explosive limits | |
| Lower explosion limit: | no data available |
| Upper explosion limit: | no data available |
| (k) Vapour pressure: | no data available |
| (l) Vapour density: | no data available |
| (m) Relative density: | no data available |
| (n) Solubility(ies) | |
| at 20 °C: | no data available |
| Soluble (g/L) in: | no data available |
| (o) Partition coefficient: n-octanol/water: | no data available |
| (p) Auto-ignition temperature: | no data available |
| (q) Decomposition temperature: | no data available |
| (r) Viscosity | |
| Kinematic viscosity: | no data available |
| Dynamic viscosity: | no data available |
| (s) Explosive properties: | not applicable |
| (t) Oxidising properties: | not applicable |

### 9.2 Other information

| | |
|---|---|
| Bulk density: | no data available |
| Refraction index: | no data available |
| Dissociation constant: | no data available |
| Surface tension: | no data available |
| Henry constant: | no data available |

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

### 10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

### 10.3 Possibility of hazardous reactions

no data available

### 10.4 Conditions to avoid

no data available

### 10.5 Incompatible materials

no data available

### 10.6 Hazardous decomposition products

no data available

### 10.7 Additional information

no data available

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

**Acute effects**
*Acute oral toxicity*:
no data available

*Acute dermal toxicity*:
no data available

*Acute inhalation toxicity*:
no data available

**Irritant and corrosive effects**
*Primary irritation to the skin:*
not applicable

*Irritation to eyes:*
not applicable

*Irritation to respiratory tract:*
not applicable

**Respiratory or skin sensitisation**
In case of skin contact: not sensitising
After inhalation: not sensitising

**STOT-single exposure**
not applicable

**STOT-repeated exposure**
not applicable

**CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
**Carcinogenicity**
No indication of human carcinogenicity.

**Germ cell mutagenicity**
No indications of human germ cell mutagenicity exist.

**Reproductive toxicity**

No indications of human reproductive toxicity exist.

**Aspiration hazard**

not applicable

**Other adverse effects**

no data available

**Additional information**

no data available

## SECTION 12: Ecological information

### 12.1 Ecotoxicity

**Acute (short-term) fish toxicity:**
no data available

**Chronic (long-term) fish toxicity**:
no data available

**Acute (short-term) daphnia toxicity:**
no data available

**Chronic (long-term) daphnia toxicity:**
no data available

**Acute (short-term) algae toxicity:**
no data available

**Chronic (long-term) algae toxicity:**
no data available

### 12.2 Persistence and degradability

no data available

### 12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data available

### 12.4 Mobility in soil:

no data available

### 12.5 Results of PBT/vPvB assessment

no data available

### 12.6 Other adverse effects

no data available

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

**Appropriate disposal / Product**
Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

**Appropriate disposal / Package**
Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

**Additional information**
no data available

## SECTION 14: Transport information

No dangerous good in sense of this transport regulation.

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

**General rules**

Water hazard class (WGK):

EU: Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC (Text with EEA relevance)

EU: Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 (Text with EEA relevance)

EU: Commission Regulation (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (Text with EEA relevance)

### 15.2 Chemical Safety Assessment

no data available

## SECTION 16: Other information

**Abbreviations and acronyms**

ACGIH - American Conference of Governmental Industrial Hygiensts
ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road
AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)
CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures
DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)
Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)
IATA-DGR - International Air Transport Association-Dangerous Goods Regulations
ICAO-TI - International Civil Aviation Organization-Technical Instructions
IMDG - International Maritime Code for Dangerous Goods
LTV - Long Term Value
NIOSH - National Institute for Occupational Safety and Health
OSHA - Occupational Safety & Health Administration
PBT - Persistent, Bioaccumulative and Toxic
RID - Regulation concerning the International Carriage of Dangerous Goods by Rail
STV - Short Term Value
SVHC - Substances of Very High Concern
vPvB - very Persistent, very Bioaccumulative

**R-phrases**

no data available

**S-phrases**

no data available

**Additional information**

Indication of changes: general update

*The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.*