



Material	23595.328
Material description	Water
Grade	HiPerSolv CHROMANORM for HPLC
CAS Number	7732-18-5
Molecular formula	H ₂ O
Molecular mass	18.02

Characteristics	Specifications
Filtered through 0.2 µm	Confirmed
Colouration	Max. 10 APHA
Evaporation residue	Max. 1 ppm
Spec. conductivity (25°C)(at filling)	Max. 1 µS/cm
Total organic carbon (TOC)	Max. 10 ppb
Absorbance (200 nm)	Max. 0.01
Absorbance (210 nm)	Max. 0.01
Absorbance (220 nm)	Max. 0.01
Absorbance (240 nm)	Max. 0.01
Absorbance (254 nm)	Max. 0.005
Absorbance (280 nm)	Max. 0.005
Absorbance (300 nm)	Max. 0.005
Fluorescence (as quinine) (254 nm)	Max. 1 ppb
Fluorescence (as quinine) (365 nm)	Max. 0.5 ppb
Gradient (210 nm)	Max. 5 mAU
Gradient (254 nm)	Max. 1 mAU

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.