



# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (amended by Regulation (EU) No 453/2010)

Revision date: 11.11.2014

Version: 4.0

Print date: 11.11.2014

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

Trade name/designation:	Legionella GVPC Selective Supplement
Product No.:	84725.0001 (VWR International)
Substance name:	
CAS No.:	
INDEX No.:	000-000-00-0
REACH registration No.:	Not yet communicated down the supply chain.
Other means of identification:	

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses:	General chemical reagent
---------------------------	--------------------------

### 1.3 Details of the supplier of the safety data sheet

Supplier (manufacturer/importer/only representative/downstream user/distributor)

#### *United Kingdom*

##### **VWR International Ltd.**

Street	Hunter Boulevard, Magna Park
Postal code/city	Lutterworth, LE17 4XN
Telephone	0800 22 33 44
Telefax	01455 55 85 86
E-mail (competent person)	vwr@sds@eu.vwr.com

##### **Emergency telephone**

Telephone	+44 (0) 1270 502894
-----------	---------------------

#### *Ireland*

##### **VWR International Ltd.**

Street	Orion Business Campus, Northwest Business Park
Postal code/city	Ballycoolin, Dublin 15
Telephone	+353 1 8822222
Telefax	+353 1 8822333
E-mail (competent person)	vwr@sds@eu.vwr.com

##### **Emergency telephone**

Telephone	+44 (0) 1270 502894
-----------	---------------------



---

## *Ireland*

### **VWR International (Northern Ireland) Ltd.**

Street	Orion Business Campus, Northwest Business Park
Postal code/city	Ballycoolin, Dublin 15
Telephone	+353 1 8822222
Telefax	+353 1 8822333
E-mail (competent person)	vwrlds@eu.vwr.com

### **Emergency telephone**

Telephone	+44 (0) 1270 502894
-----------	---------------------

---

## *Netherlands*

### **VWR International B.V.**

Street	Basisweg 34
Postal code/city	1043 AP Amsterdam
Telephone	+32 16 385 011
Telefax	+32 16 385 385
E-mail (competent person)	vwrlds@eu.vwr.com

### **Emergency telephone**

Telephone	+44 (0) 1270 502894
-----------	---------------------

---

## *Switzerland*

### **VWR International GmbH**

Street	Lerzenstrasse 16/18
Postal code/city	8953 Dietikon
Telephone	+44 (0) 745 13 13
Telefax	+44 (0) 745 13 10
E-mail (competent person)	vwrlds@eu.vwr.com

### **Emergency telephone**

Telephone	145
-----------	-----



## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

#### 2.1.1 Classification according to Regulation (EC) No. 1272/2008 [CLP]

Hazard classes and hazard categories	Hazard statements
Germ cell mutagenicity, category 2	H341
Reproductive toxicity, category 1B	H360
Acute toxicity, category 2, oral	H300
Hazardous to the aquatic environment, chronic, category 3	H412

### 2.2 Label elements

#### 2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms



**Signal word:** Danger

Hazard statements	
H341	Suspected of causing genetic defects.
H360	May damage fertility or the unborn child.
H300	Fatal if swallowed.
H412	Harmful to aquatic life with long lasting effects.

Precautionary statements	
P201	Obtain special instructions before use.
P281	Use personal protective equipment as required.
P273	Avoid release to the environment.
P309+P310	IF exposed or if you feel unwell: Immediately call a POISON CENTER or doctor/physician.

Other hazards

SVHC No



## SECTION 3: Composition / information on ingredients

### 3.1 Substances

not relevant (Product identifier)

### 3.2 Mixtures

Hazardous ingredients Classification according to Regulation (EC) No. 1272/2008 [CLP]

Substance name	Concentration	Product identifier	Hazard classes and hazard categories
Cycloheximide	2,5-7%	CAS No.: 66-81-9 EC No.: 200-636-0 REACH No.: Not yet communicated down the supply chain.	Germ cell mutagenicity, category 2 - H341 Reproductive toxicity, category 1B - H360 Acute toxicity, category 2, oral - H300 Hazardous to the aquatic environment, chronic, category 2 - H411

## SECTION 4: First aid measures

### 4.1 General information

IF exposed: Immediately call a POISON CENTRE/doctor/.... If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

#### After inhalation

Immediately call a POISON CENTRE/doctor/.... Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

#### In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

#### After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

#### In case of ingestion

Immediately call a POISON CENTRE/doctor/.... Do NOT induce vomiting. Rinse mouth thoroughly with water. Give nothing to eat or drink.

### 4.2 Most important symptoms and effects, both acute and delayed

no data available

### 4.3 Indication of any immediate medical attention and special treatment needed

no data available

### 4.4 Self-protection of the first aider

First aider: Pay attention to self-protection!

### 4.5 Information to physician

no data available

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### Suitable extinguishing media

The product itself does not burn. Co-ordinate fire-fighting measures to the fire surroundings.

**Extinguishing media which must not be used for safety reasons**

no restriction

## **5.2 Special hazards arising from the substance or mixture**

In case of fire may be liberated: Carbon dioxide (CO<sub>2</sub>) Carbon monoxide Nitrogen oxides (NO<sub>x</sub>) Sulphur oxides

## **5.3 Advice for firefighters**

DO NOT fight fire when fire reaches explosives. In case of fire: Wear self-contained breathing apparatus.

## **5.4 Additional information**

Do not allow run-off from fire-fighting to enter drains or water courses. Do not inhale explosion and combustion gases. Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen. Use water spray jet to protect personnel and to cool endangered containers.

# **SECTION 6: Accidental release measures**

## **6.1 Personal precautions, protective equipment and emergency procedures**

Avoid generation of dust. Do not breathe dust. Provide adequate ventilation. Use personal protection equipment. In case of major fire and large quantities: Remove persons to safety.

## **6.2 Environmental precautions**

Do not allow to enter into surface water or drains. Make sure spills can be contained, e.g. in sump pallets or kerbed areas. Discharge into the environment must be avoided.

## **6.3 Methods and material for containment and cleaning up**

Spilled product must never be returned to the original container for recycling. Take up dust-free and set down dust-free. Collect in closed and suitable containers for disposal.

## **6.4 Additional information**

Clear spills immediately.

# **SECTION 7: Handling and storage**

## **7.1 Precautions for safe handling**

Avoid exposure - obtain special instructions before use. Avoid: Inhalation Avoid contact with skin and eyes. Provide adequate ventilation as well as local exhaust at critical locations. Usual measures for fire prevention. Protect from moisture.

## **7.2 Conditions for safe storage, including any incompatibilities**

storage temperature: 15-25 °C

Storage class:

Keep container tightly closed in a cool, well-ventilated place.

## **7.3 Specific end use(s)**

no data available

# **SECTION 8: Exposure controls/personal protection**

## **8.1 Control parameters**

Does not contain substances above concentration limits fixing an occupational exposure limit.

## **8.2 Exposure controls**

### **8.2.1 Appropriate engineering controls**

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.



### 8.2.2 Personal protection equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn. For the protection against direct skin contact, body protective clothing is essential (in addition to the usual working clothes).

#### *Eye/face protection*

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

Recommendation: VWR 111-0432

#### *Skin protection*

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms: DIN EN 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.

#### By short-term hand contact

Suitable material: NBR (Nitrile rubber)

Thickness of the glove material: 0,12 mm

Breakthrough time (maximum wearing time): > 480 min

Recommended glove articles: VWR 112-0998

#### By long-term hand contact

Suitable material: NBR (Nitrile rubber)

Thickness of the glove material: 0,38 mm

Breakthrough time (maximum wearing time): > 480 min

Recommended glove articles: VWR 112-3717 / 112-1381

#### *Respiratory protection*

Respiratory protection necessary at: aerosol or mist formation

Suitable respiratory protection apparatus: Filtering Half-face mask (DIN EN 149)

Recommendation: VWR 111-0451

Suitable material: P3

Recommendation: no data available

#### *Additional information*

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

### 8.2.3 Environmental exposure controls

no data available

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	solid
Colour:	white
(b) Odour:	no data available
(c) Odour threshold:	no data available

#### Safety relevant basic data

(d) pH:	no data available
(e) Melting point/freezing point:	no data available
(f) Initial boiling point and boiling range:	no data available
(g) Flash point:	no data available
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	not applicable
(j) Upper/lower flammability or explosive limits	
Lower explosion limit:	no data available
Upper explosion limit:	no data available
(k) Vapour pressure:	no data available
(l) Vapour density:	no data available
(m) Relative density:	no data available
(n) Solubility(ies)	
at 20 °C:	no data available
Soluble (g/L) in:	no data available
(o) Partition coefficient: n-octanol/water:	no data available
(p) Auto-ignition temperature:	no data available
(q) Decomposition temperature:	no data available
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	no data available
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable

### 9.2 Other information

Bulk density:	no data available
Refraction index:	no data available
Dissociation constant:	no data available
Surface tension:	no data available
Henry constant:	no data available

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

### 10.2 Chemical stability

no data available

### 10.3 Possibility of hazardous reactions

no data available

### 10.4 Conditions to avoid

no data available

### 10.5 Incompatible materials

no data available

### 10.6 Hazardous decomposition products

no data available

### 10.7 Additional information

no data available

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute effects

*Acute oral toxicity:*

no data available

*Acute dermal toxicity:*

no data available

*Acute inhalation toxicity:*

no data available

#### Irritant and corrosive effects

*Primary irritation to the skin:*

not applicable

*Irritation to eyes:*

not applicable

*Irritation to respiratory tract:*

not applicable

#### Respiratory or skin sensitisation

In case of skin contact: not sensitising

After inhalation: not sensitising

#### STOT-single exposure

not applicable

#### STOT-repeated exposure

not applicable

#### CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

##### Carcinogenicity

No indication of human carcinogenicity.

##### Germ cell mutagenicity

Suspected of causing genetic defects.



**Reproductive toxicity**

May damage fertility or the unborn child.

**Aspiration hazard**

not applicable

**Other adverse effects**

no data available

**Additional information**

no data available

## SECTION 12: Ecological information

### 12.1 Ecotoxicity

**Acute (short-term) fish toxicity:**

no data available

**Chronic (long-term) fish toxicity:**

no data available

**Acute (short-term) daphnia toxicity:**

no data available

**Chronic (long-term) daphnia toxicity:**

no data available

**Acute (short-term) algae toxicity:**

no data available

**Chronic (long-term) algae toxicity:**

no data available

### 12.2 Persistence and degradability

no data available

### 12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data available

### 12.4 Mobility in soil:

no data available

### 12.5 Results of PBT/vPvB assessment

no data available

### 12.6 Other adverse effects

no data available

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

#### Appropriate disposal / Product

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal. Send to a hazardous waste incinerator facility under observation of official regulations.

Waste code product: no data available

#### Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

#### Additional information

no data available

## SECTION 14: Transport information

### Land transport (ADR/RID)

14.1	UN-No.:	2811
14.2	Proper Shipping Name:	TOXIC SOLID, ORGANIC, N.O.S. (CYCLOHEXIMIDE)
14.3	Class(es):	6.1
	Classification code:	T2
	Hazard label(s):	6.1
14.4	Packing group:	II
14.5	Environmental hazards:	Nein
14.6	Special precautions for user:	
	Hazard identification number (Kemler No.):	60
	tunnel restriction code:	D/E
		(Passage forbidden through tunnels of category D when carried in bulk or in tanks. Passage forbidden through tunnels of category E.)

### Sea transport (IMDG)

14.1	UN-No.:	2811
14.2	Proper Shipping Name:	TOXIC SOLID, ORGANIC, N.O.S. (CYCLOHEXIMIDE)
14.3	Class(es):	6.1
	Classification code:	
	Hazard label(s):	6.1
14.4	Packing group:	II
14.5	Environmental hazards:	Nein
	MARINE POLLUTANT:	No
14.6	Special precautions for user:	
	Segregation group:	-
	EmS-No.	F-A S-A
14.7	Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	
	not relevant	



## Air transport (ICAO-TI / IATA-DGR)

14.1	UN-No.:	2811
14.2	Proper Shipping Name:	TOXIC SOLID, ORGANIC, N.O.S. (CYCLOHEXIMIDE)
14.3	Class(es):	6.1
	Classification code:	T2
	Hazard label(s):	6.1
14.4	Packing group:	II
14.5	Special precautions for user	not relevant

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### General rules

Water hazard class (WGK):

EU: Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC (Text with EEA relevance)

EU: Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 (Text with EEA relevance)

EU: Commission Regulation (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (Text with EEA relevance)

### 15.2 Chemical Safety Assessment

no data available



## SECTION 16: Other information

### Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists  
ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road  
AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)  
CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures  
DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)  
Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)  
IATA-DGR - International Air Transport Association-Dangerous Goods Regulations  
ICAO-TI - International Civil Aviation Organization-Technical Instructions  
IMDG - International Maritime Code for Dangerous Goods  
LTV - Long Term Value  
NIOSH - National Institute for Occupational Safety and Health  
OSHA - Occupational Safety & Health Administration  
PBT - Persistent, Bioaccumulative and Toxic  
RID - Regulation concerning the International Carriage of Dangerous Goods by Rail  
STV - Short Term Value  
SVHC - Substances of Very High Concern  
vPvB - very Persistent, very Bioaccumulative

### R-phrases

no data available

### S-phrases

no data available

### Additional information

Indication of changes:                      general update

*The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.*