Product Specification

Material	24379.363
Material description	D(+)-Glucose anhydrous
Grade	GPR RECTAPUR
CAS Number	50-99-7
Molecular formula	C6H12O6
Molecular mass	180.16

Characteristics	Specifications
Spec. opt. rotation (calc. on anhydrous)	52.5 --> 53.3 °
Loss on drying (100°C)	Max. 1.0 %
Ignition residue (SO4)	Max. 0.1 %
Cl (Chloride)	Max. 100 ppm

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Anja Vanhalle, Head of Laboratory - Haasrode
VWR International bvba; Geldenaaksebaan 464; BE-3001 Leuven; Belgium

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.