



| | |
|----------------------|---|
| Material | 24379.294 |
| Material description | D(+)-Glucose anhydrous |
| Grade | GPR RECTAPUR |
| CAS Number | 50-99-7 |
| Molecular formula | C ₆ H ₁₂ O ₆ |
| Molecular mass | 180.16 |

| Characteristics | Specifications |
|--|-----------------|
| Spec. opt. rotation (calc. on anhydrous) | 52.5 --> 53.3 ° |
| Loss on drying (100°C) | Max. 1.0 % |
| Ignition residue (SO ₄) | Max. 0.1 % |
| Cl (Chloride) | Max. 100 ppm |

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Anja Vanhalle, Head of Laboratory - Haasrode
VWR International bvba; Geldenaaksebaan 464; BE-3001
Leuven; Belgium

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.