



Material	24549.554
Material description	n-Heptane
Grade	GPR RECTAPUR
CAS Number	142-82-5
Molecular formula	C ₇ H ₁₆
Molecular mass	100.21

Characteristics	Specifications
Assay	Min. 99.0 %
IR Spectrum	Passes test
Boiling point	98 → 99 °C
Density (20/4)	0.681 → 0.685
Acidity	Max. 0.0008 meq/g
Substances coloured by H ₂ SO ₄	Max. 90 APHA
Evaporation residue	Max. 20 ppm

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.