

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (amended by Regulation (EU) No 453/2010)

Revision date: 19.06.2015

Version: 4.0

Print date: 19.06.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name/designation:	m-Endo LES agar
Product No.:	84645.0500 (VWR International)
Substance name:	
CAS No.:	00-00-0
INDEX No.:	000-000-00-0
REACH registration No.:	Not yet communicated down the supply chain.
Other means of identification:	

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses:	General chemical reagent
---------------------------	--------------------------

1.3 Details of the supplier of the safety data sheet

Supplier (manufacturer/importer/only representative/downstream user/distributor)

United Kingdom

VWR International Ltd.

Street	Hunter Boulevard, Magna Park
Postal code/city	Lutterworth, LE17 4XN
Telephone	0800 22 33 44
Telefax	01455 55 85 86
E-mail (competent person)	SDS@eu.vwr.com

Emergency telephone

Telephone	+44 (0) 1270 502894
-----------	---------------------

Ireland

VWR International Ltd.

Street	Orion Business Campus, Northwest Business Park
Postal code/city	Ballycoolin, Dublin 15
Telephone	+353 1 8822222
Telefax	+353 1 8822333
E-mail (competent person)	SDS@eu.vwr.com

Emergency telephone

Telephone	+44 (0) 1270 502894
-----------	---------------------

Ireland

VWR International (Northern Ireland) Ltd.

Street	Orion Business Campus, Northwest Business Park
Postal code/city	Ballycoolin, Dublin 15
Telephone	+353 1 8822222
Telefax	+353 1 8822333
E-mail (competent person)	SDS@eu.vwr.com

Emergency telephone

Telephone	+44 (0) 1270 502894
-----------	---------------------

Netherlands

VWR International B.V.

Street	Basisweg 34
Postal code/city	1043 AP Amsterdam
Telephone	+32 16 385 011
Telefax	+32 16 385 385
E-mail (competent person)	SDS@eu.vwr.com

Emergency telephone

Telephone	030 2748888 (Nationaal Vergiftigingen Informatie Centrum (NVIC), uitsluitend bestemd om professionele hulpverleners te informeren bij acute vergiftigingen).
-----------	--

Switzerland

VWR International GmbH

Street	Lerzenstrasse 16/18
Postal code/city	8953 Dietikon
Telephone	+44 (0) 745 13 13
Telefax	+44 (0) 745 13 10
E-mail (competent person)	SDS@eu.vwr.com

Emergency telephone

Telephone	145
-----------	-----

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

2.1.1 Classification according to Regulation (EC) No. 1272/2008 [CLP]

Hazard classes and hazard categories	Hazard statements
Carcinogenicity, category 1B	H350

2.1.2 Classification according to Directive 67/548/EEC or 1999/45/EC

T	Carcinogenic Cat. 1 (Carc. Cat. 1)	R45
---	------------------------------------	-----

2.2 Label elements

2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms



Signal word: Danger

Hazard statements	
H350	May cause cancer.

Precautionary statements	
P201	Obtain special instructions before use.
P281	Use personal protective equipment as required.
P308+P313	IF exposed or concerned: Get medical advice/attention.

2.2.2 Labelling (67/548/EEC or 1999/45/EC)

Hazard symbols

T

R-phrases	
R45	May cause cancer.

S-phrases	
S53	Avoid exposure - obtain special instructions before use.
S45	In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

Other hazards

SVHC No

SECTION 3: Composition / information on ingredients

3.1 Substances

not applicable

3.2 Mixtures

Hazardous ingredients Classification according to Regulation (EC) No. 1272/2008 [CLP]

Substance name	Concentration	Product identifier	Hazard classes and hazard categories
Pararosaniline hydrochloride	1-10%	CAS No.: EC No.: REACH No.: Not yet communicated down the supply chain.	Carcinogenicity, category 1B - H350
di-Potassium disulphite	1-5%	CAS No.: EC No.: REACH No.: Not yet communicated down the supply chain.	Specific target organ toxicity (single exposure), category 3, vascular - H335 Serious eye damage, category 1 - H318

Hazardous ingredients Classification according to 67/548/EEC

Substance name	Concentration	Product identifier	Hazard classes and hazard categories
Pararosaniline hydrochloride	1-10%	CAS No.: EC No.: REACH No.: Not yet communicated down the supply chain.	T, Carcinogenic Cat. 1 (Carc. Cat. 1), R45
di-Potassium disulphite	1-5%	CAS No.: EC No.: REACH No.: Not yet communicated down the supply chain.	R31 Xi, Irritant, R37 Xi, Irritant, R41

SECTION 4: First aid measures

4.1 General information

IF exposed or if you feel unwell: Call a POISON CENTRE or doctor/physician. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

After inhalation

Call a POISON CENTRE/doctor/.... Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

In case of ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

4.2 Most important symptoms and effects, both acute and delayed

no data available

4.3 Indication of any immediate medical attention and special treatment needed

no data available

4.4 Self-protection of the first aider

First aider: Pay attention to self-protection!

4.5 Information to physician

no data available

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Co-ordinate fire-fighting measures to the fire surroundings.

Extinguishing media which must not be used for safety reasons

no data available

5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated: Pyrolysis products, toxic

5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives. In case of fire: Wear self-contained breathing apparatus.

5.4 Additional information

Do not allow run-off from fire-fighting to enter drains or water courses. Do not inhale explosion and combustion gases. Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen. Use water spray jet to protect personnel and to cool endangered containers.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety. Use personal protection equipment. Stop leak if safe to do so. Eliminate all ignition sources if safe to do so.

6.2 Environmental precautions

Do not allow to enter into surface water or drains. Discharge into the environment must be avoided. Ensure waste is collected and contained.

6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Clean contaminated objects and areas thoroughly observing environmental regulations. Collect in closed and suitable containers for disposal.

6.4 Additional information

Clear spills immediately.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

All work processes must always be designed so that the following is as low as possible: Inhalation skin contact Eye contact Use extractor hood (laboratory). If handled uncovered, arrangements with local exhaust ventilation have to be used. If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

7.2 Conditions for safe storage, including any incompatibilities

storage temperature: 15-25 °C

Storage class: 6.1A

Keep container tightly closed in a cool, well-ventilated place.

7.3 Specific end use(s)

no data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

8.2.2 Personal protection equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn. For the protection against direct skin contact, body protective clothing is essential (in addition to the usual working clothes).

Eye/face protection

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

Recommendation: VWR 111-0432

Skin protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms: DIN EN 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.

By short-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,12 mm
Breakthrough time (maximum wearing time):	> 480 min
Recommended glove articles:	VWR 112-0998

By long-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,38 mm
Breakthrough time (maximum wearing time):	> 480 min
Recommended glove articles:	VWR 112-3717 / 112-1381

Respiratory protection

no data available

Suitable respiratory protection apparatus:

Recommendation: no data available

Suitable material: no data available

Recommendation: no data available

Additional information

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

8.2.3 Environmental exposure controls

no data available

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

- | | |
|----------------------|--------|
| (a) Appearance | |
| Physical state: | solid |
| Colour: | violet |
| (b) Odour: | |
| no data available | |
| (c) Odour threshold: | |
| no data available | |

Safety relevant basic data

- | | |
|--|-------------------|
| (d) pH: | no data available |
| (e) Melting point/freezing point: | no data available |
| (f) Initial boiling point and boiling range: | no data available |
| (g) Flash point: | no data available |
| (h) Evaporation rate: | no data available |
| (i) Flammability (solid, gas): | not applicable |
| (j) Upper/lower flammability or explosive limits | |
| Lower explosion limit: | no data available |
| Upper explosion limit: | no data available |
| (k) Vapour pressure: | no data available |
| (l) Vapour density: | no data available |
| (m) Relative density: | no data available |
| (n) Solubility(ies) | |
| at 20 °C: | no data available |
| Soluble (g/L) in: | no data available |
| (o) Partition coefficient: n-octanol/water: | no data available |
| (p) Auto-ignition temperature: | no data available |
| (q) Decomposition temperature: | no data available |
| (r) Viscosity | |
| Kinematic viscosity: | no data available |
| Dynamic viscosity: | no data available |
| (s) Explosive properties: | not applicable |
| (t) Oxidising properties: | not applicable |

9.2 Other information

Bulk density: no data available

Refraction index:	no data available
Dissociation constant:	no data available
Surface tension:	no data available
Henry constant:	no data available

SECTION 10: Stability and reactivity

10.1 Reactivity

no data available

10.2 Chemical stability

no data available

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

no data available

10.6 Hazardous decomposition products

no data available

10.7 Additional information

no data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:

no data available

Acute dermal toxicity:

no data available

Acute inhalation toxicity:

no data available

Irritant and corrosive effects

Primary irritation to the skin:

not applicable

Irritation to eyes:

not applicable

Irritation to respiratory tract:

not applicable

Respiratory or skin sensitisation

In case of skin contact: not sensitising

After inhalation: not sensitising

STOT-single exposure

not applicable

STOT-repeated exposure

not applicable

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Carcinogenicity

May cause cancer.

Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.

Reproductive toxicity

No indications of human reproductive toxicity exist.

Aspiration hazard

not applicable

Other adverse effects

no data available

Additional information

no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Acute (short-term) fish toxicity:

no data available

Chronic (long-term) fish toxicity:

no data available

Acute (short-term) daphnia toxicity:

no data available

Chronic (long-term) daphnia toxicity:

no data available

Acute (short-term) algae toxicity:

no data available

Chronic (long-term) algae toxicity:

no data available

12.2 Persistence and degradability

no data available



12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data available

12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

no data available

12.6 Other adverse effects

no data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Appropriate disposal / Product

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

Additional information

no data available

SECTION 14: Transport information

Land transport (ADR/RID)

No dangerous good in sense of this transport regulation.

Sea transport (IMDG)

No dangerous good in sense of this transport regulation.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code
not relevant

Air transport (ICAO-TI / IATA-DGR)

No dangerous good in sense of this transport regulation.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

General rules

Water hazard class (WGK): strongly hazardous to water (WGK 3)

EU: Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC (Text with EEA relevance)

EU: Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 (Text with EEA relevance)

EU: Commission Regulation (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (Text with EEA relevance)

15.2 Chemical Safety Assessment

no data available

SECTION 16: Other information

Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists

ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road

AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)

CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures

DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)

Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)

IATA-DGR - International Air Transport Association-Dangerous Goods Regulations

ICAO-TI - International Civil Aviation Organization-Technical Instructions

IMDG - International Maritime Code for Dangerous Goods

LTV - Long Term Value

NIOSH - National Institute for Occupational Safety and Health

OSHA - Occupational Safety & Health Administration

PBT - Persistent, Bioaccumulative and Toxic

RID - Regulation concerning the International Carriage of Dangerous Goods by Rail

STV - Short Term Value

SVHC - Substances of Very High Concern

vPvB - very Persistent, very Bioaccumulative

Additional information

Indication of changes: general update

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

