



Material	83627.320
Material description	Chloroform
Grade	HiPerSolv CHROMANORM
CAS Number	67-66-3

Characteristics	Specifications
Assay (+ stabilizing agent)	Min. 99.8 %
Stabilizer (Ethanol)	Confirmed
Acidity	Max. 0.0005 meq/g
Alkalinity	Max. 0.0002 meq/g
Evaporation residue	Max. 10 ppm
Water	Max. 0.05 %
Absorbance (250 nm)	Max. 0.3
Absorbance (260 nm)	Max. 0.1
Absorbance (280 nm)	Max. 0.02
Absorbance (300 nm)	Max. 0.01
Transmittance (250 nm)	Min. 50 %
Transmittance (260 nm)	Min. 84 %
Transmittance (280 nm)	Min. 95 %
Transmittance (300 nm)	Min. 98 %
Filtered through 0.2 µm	Confirmed
Packaged under nitrogen	Confirmed

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.