



Sharpsafe® 7 Liter

SHA-41105430



Scalpel blade
remover

Insulin pen
remover



Luer-Slip

Luer-Lock

Unobstructed opening +
Safety flap

Features

- The container consists of two parts: a yellow body and translucent lid
- Safe, quick and simple 4 pressures assembly with 4 audible « click »
- Large « headroom » considered for the user as the safety area: 6 cm from the lid to the fill line
- Disconnection for all types of needle even for the scalpel blade and insulin pen
- Safety flap for extra protection (Option without Ref. : SHA-41106610*)
- 2 closure positions on the flip top lid: temporary and final closure
- Reopening of the temporary closure with a simple finger pressure on the lid
- Possibility to block the lid in the open position
- Clearly visible fill line on the translucent lid
- In-mould label which cannot be removed, even by autoclaving
- Handle for a safe transport
- Can be used in a “single hand” way
- Accessories: Stands, hooks and brackets available
- Instruction of use on the label in French and Dutch (also available in English)
- Autoclaving valid to 135°C during 20 minutes for an empty and open container
- Conform to the NFX30-500 and BS7320 in terms of resistance to penetration, drop impact and liquid resistance. ADR and NF302 certificated. Holder of the brand NF302 (details see reverse)
- Origin of the product: European Union



Sharpsafe® 7 Liter

SHA-41105430








Technical Information

- **Material:** Polypropylene
- **Max. nominal volume:** 6,7 L
- **Max. filling capacity:** 5,6 L
- **Dimensions opening:** 55 x 50 mm
- **Dimensions flip top closed:** 380 x 175 x 175 mm (HxLxW)
- **Weight:** 0,43 kg

Packaging

- **Quantity per box:** 50
- **Dimensions box (HxLxW):** 678 x 804 x 340 mm
- **Weight:** 23,10 kg
- **Volume:** 0,185 m³
- **Box per pallet:** 9
- **Pallet dimensions:** 220 x 120 x 80 cm
- **Pallet weight:** 228 kg

Conformity

	The NF-X-30-500 is the latest Sharps-guideline in Europe and the most rigorous European standard in terms of resistance to penetration, drop impact, perforation and liquid resistance
	The NF302 (Norme française) ensures the continued existence of the standards defined by NF-X-30-500. The „Laboratoire National d'Essais“ (French Institute for Standards) checks regularly the quality of the products on the market.
	The British Standard BS 7320 sets rigorous standards in terms of resistance to penetration, drop impact, perforation and liquid resistance. The BS7320 is certificated via Kitemark.
	In conformity with A.D.R. and UN3291: International norm for the transport of dangerous material and infectious waste.
	The TRBA 250 is a German guideline for the treatment of biological, dangerous and infectious waste.
	Autoclave at 135°C during 20 min.
	Quality management system: ISO 9001:2008 and ISO 13485:2003 Environmental Standard: ISO 14001:2004