

### SECTION 1 IDENTIFICATION

#### PRODUCT IDENTIFIER

**PRODUCT NAME:** RED BORDER LABEL TAPE

**PRODUCT CODE:** P/Ns RB-501 RB-502 RB-534 RB-5112

Recommended Use: Self-adhesive removable label tape used for labeling.

**MANUFACTURER:** PDC Healthcare

27770 North Entertainment Drive, Suite 200, Valencia, CA 91355 USA

**TELEPHONE:** USA: 661 257 0233, International: +32 67 89 56 56

### SECTION 2 HAZARD(S) IDENTIFICATION

**EMERGENCY OVERVIEW:** No significant health hazards associated with this product during normal use conditions.

May cause skin or eye irritation by mechanical abrasion or by sensitivity to polymers.

Note: If this product is subject to combustion it will undergo hazardous decomposition that will yield the formation and release of hazardous substances including but not limited to carbon dioxide, carbon monoxide, polycyclic organic matter, and smoke. Exposure may cause irritation of the eyes, skin, and respiratory tract. Symptoms such as coughing, tearing, and irritation should be regarded as potentially hazardous and measures should be taken to avoid exposure.

#### ROUTE OF EXPOSURE:

**Eye Contact:** May cause eye irritation by mechanical abrasion.

**Skin Contact:** May cause skin irritation by sensitivity to polymers.

**Ingestion:** May be harmful if swallowed.

**Inhalation:** Not an expected route of exposure.

**Chronic Health Effects:** Prolonged or repeated contact may cause skin irritation.

**Signs/Symptoms:** Signs and symptoms for overexposure – none known

**Target Organs** Eyes, Skin, Digestive System

**Aggravation of** None known

**Pre-Existing Conditions:**

### SECTION 3 COMPOSITION/information on ingredients

Ingredient	CAS #	% by Wt
Synthetic Latex Saturated Paper	proprietary	50-60 %
Rubber Adhesive	proprietary	40-50 %

### SECTION 4 FIRST-AID MEASURES

**After Eye Contact:** If wearing contact lenses, remove. Hold eyelids apart and immediately flush eyes with plenty of low-pressure water for at least 15 minutes. Get medical attention if irritation persists.

**After Skin Contact:** Wash skin thoroughly with soap and water. Seek medical attention if irritation develops or persists.

**After Ingestion:** Seek immediate medical advice.

**After Inhalation:** Not an expected route of exposure.

**Note to Physician:** If irritation or symptoms occur, treat symptomatically. No further relevant information available.

### SECTION 5 FIRE FIGHTING MEASURES

#### SUITABLE EXTINGUISHING

**MEDIA:** Foam, Water Spray, CO2, or Dry Chemical.

#### UNSUITABLE EXTINGUISHING

**MEDIA:** None known

<b>PROTECTIVE EQUIPMENT:</b>	Wear a self-contained breathing apparatus with a full face piece operated in the positive pressure demand mode with appropriate turn-out gear and chemical resistant personal protective equipment.
<b>HAZARDOUS COMBUSTION BYPRODUCTS:</b>	If this product is subject to combustion it will undergo hazardous decomposition that will yield the formation and release of hazardous substances including but not limited to carbon dioxide, carbon monoxide, polycyclic organic matter, and smoke.
<b>SPECIFIC HAZARD FIRE/EXPOSION:</b>	Minimal fire hazard as supplied. Polymers in adhesive and polymer backed cloth will support combustion/

### SECTION 6 ACCIDENTAL RELEASE MEASURES

Keep away from ignition sources.  
Environmental precautions: Do not allow to enter sewers / surface or ground water.  
Methods for containment/cleanup: Sweep or pickup. Discard damaged or contaminated product.  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### SECTION 7 HANDLING AND STORAGE

<b>Storage:</b>	Store in a cool dry place. Avoid extreme heat, cold, or humidity.
<b>Handling:</b>	Material will be tacky/sticky. Recommend the use of lightweight cloth or leather gloves for actual handling of material.

### SECTION 8 EXPOSURE CONTROLS / PERSONAL PROTECTION

Avoid contact with eyes and skin. Keep pressure sensitive tape away from food stuffs, beverages, and feed.  
Adhesive on tape is not intended for direct or indirect food contact.

<b>Exposure guidelines:</b>	Not applicable
<b>Eye Protection:</b>	Safety glasses with side-shields recommended.
<b>Skin Protection:</b>	Normal lightweight work clothing will minimize skin contact. Use of lightweight cloth or leather gloves recommended.
<b>Respiratory Protractions:</b>	No adverse respiratory exposure anticipated under normal use.
<b>Engineering Controls:</b>	No special engineering controls are required.

### SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	White with Red Border	<b>Vapor Density</b>	Not applicable
<b>Odor:</b>	No Strong Odor	<b>Relative Density:</b>	Not Determined
<b>Odor Threshold:</b>	Not Applicable	<b>Flashpoint:</b>	Not Determined
<b>pH:</b>	Not applicable	<b>Evaporation Rate</b>	Not applicable
<b>Solubility – Water (H<sub>2</sub>O):</b>	negligible	<b>Flammability (solid, gas);</b>	Combustible solid.
<b>Melting Point:</b>	>100°C	<b>Auto-ignition temperature:</b>	Not Determined
<b>Freezing Point:</b>	Not applicable	<b>Decomposition temperature:</b>	Not Determined
<b>Initial Boiling Point and Boiling Range:</b>	Not applicable	<b>Percent Volatiles:</b>	<1%
<b>Vapor Pressure</b>	Not applicable	<b>Upper/lower flammability or explosive limits;</b>	Not Determined

### SECTION 10 STABILITY AND REACTIVITY

<b>Chemical Stability:</b>	Stable under normal conditions.
<b>Possibility of Hazardous Reactions:</b>	No dangerous reactions known.
<b>Conditions to Avoid:</b>	Source of ignition, heat or flame.
<b>Incompatible Materials:</b>	Strong acids, oxidizing agents.

**Hazardous Decomposition Products:** If this product is subject to combustion it will undergo hazardous decomposition that will yield the formation and release of hazardous substances including but not limited to carbon dioxide, carbon monoxide, polycyclic organic matter and particulate matter.

### SECTION 11 TOXICOLOGICAL INFORMATION

Not determined. May cause skin or eye irritation by mechanical abrasion or by sensitivity to polymers. May be harmful if swallowed.

**SECTION 12 ECOLOGICAL INFORMATION**

Not determined

**SECTION 13 DISPOSAL CONSIDERATIONS**

Dispose in accordance with federal, state and local regulations. Do not allow to enter waterway, sewer or drain.

**SECTION 14 TRANSPORT INFORMATION**

Not a hazardous material when shipped.

**SECTION 15 REGULATORY INFORMATION**

OSHA: As defined by 29 CFR 1910. 1200, this product is considered to be an article, defined in the regulation as a "manufactured item other than a fluid or particle: (I) which is formed to a specific shape or design during manufacture; (II) has an end use function(s) dependent in whole or in part upon its shape or design during end use; and (III) which does not release more than very small quantities, e.g., minimal or trace amounts of a hazardous chemical, and does not pose a physical hazard or health risk to employees."

California Proposition 65: To the best of our knowledge, this product does not contain chemicals known to the State of California to cause cancer or reproductive toxicity ("Proposition 65 Chemicals") at levels which would require a warning.

H.R. 4173 Conflict Mineral: To the best of our knowledge this product does not contain Tungsten, Tantalum, Gold and Tin as intentional raw materials or in the manufacturing process of the raw materials. Additionally, raw materials used to manufacture these products are not sourced from Democratic Republic of Congo or adjoining countries.

EU Directive 2011/65/EU & 2012/19/EU: Pressure sensitive tape is outside the scope of the requirements set forth by European Union Directive 2011/65/EU – ROHS II and the European Union Directive 2012/19/EU – WEEE relating to electronics and electrical equipment which bans or limits certain heavy metals and polybrominated flame retardants. However, raw material vendor has confirmed that due diligence has been performed through careful review of raw material specifications, vendor certifications and random testing to insure its product does not contain heavy metals, Polybrominated Biphenyls (PBBs), or Polybrominated Diphenyl Ethers (PDBEs) as unintended impurities in concentration exceeding EU regulatory limits.

EU Article 3(3) of Regulation (EC) 1907/2006 (REACH): This product is an article as defined by Article 3(3) of Regulation (EC) 1907/2006 (REACH). As an article, this product is not subject to the Safety Data Sheet requirements outlined in Article 33(1) of the same Regulation. This product does not have an intended release of a chemical substance, is not a chemical mixture, and is not subject to pre-registration or the registration process. This product contains no "substances of very high concern" (SVHC) in a concentration above 0.1% (w/w) (REACH Article 59) on the Candidate List of Substances of Very High Concern (REACH Annex XIV). PDC continues to monitor the SVHC list and its updates.

**SECTION 16: OTHER INFORMATION**

SDS ISSUE DATE: July 9, 2014

**DISCLAIMER:**

The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. PDC MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the product is fit for a particular purpose and suitable for user's method of use or application. PDC make no representations as to the completeness or accuracy of this SDS.