



Material	83877.260
Material description	Water
Grade	NORMATOM for trace metal analysis
CAS Number	7732-18-5
Molecular formula	H ₂ O
Molecular mass	18.02

Characteristics	Specifications
Colouration	≤ 10 APHA
Ag (Silver)	≤ 50 ppt
Al (Aluminium)	≤ 200 ppt
As (Arsenic)	≤ 50 ppt
Au (Gold)	≤ 50 ppt
B (Boron)	≤ 500 ppt
Ba (Barium)	≤ 50 ppt
Be (Beryllium)	≤ 50 ppt
Bi (Bismuth)	≤ 50 ppt
Ca (Calcium)	≤ 500 ppt
Cd (Cadmium)	≤ 50 ppt
Ce (Cerium)	≤ 20 ppt
Co (Cobalt)	≤ 50 ppt
Cr (Chromium)	≤ 50 ppt
Cs (Cesium)	≤ 50 ppt
Cu (Copper)	≤ 100 ppt
Dy (Dysprosium)	≤ 20 ppt
Er (Erbium)	≤ 20 ppt
Eu (Europium)	≤ 20 ppt
Fe (Iron)	≤ 300 ppt
Ga (Gallium)	≤ 50 ppt
Gd (Gadolinium)	≤ 20 ppt
Ge (Germanium)	≤ 50 ppt
Hf (Hafnium)	≤ 10 ppt
Hg (Mercury)	≤ 200 ppt
Ho (Holmium)	≤ 20 ppt
In (Indium)	≤ 50 ppt
K (Potassium)	≤ 300 ppt

>>> Continued on page 2 >>>



Characteristics	Specifications
La (Lanthanum)	≤ 20 ppt
Li (Lithium)	≤ 50 ppt
Lu (Lutetium)	≤ 20 ppt
Mg (Magnesium)	≤ 100 ppt
Mn (Manganese)	≤ 50 ppt
Mo (Molybdenum)	≤ 50 ppt
Na (Sodium)	≤ 500 ppt
Nb (Niobium)	≤ 20 ppt
Nd (Neodymium)	≤ 20 ppt
Ni (Nickel)	≤ 50 ppt
Pb (Lead)	≤ 50 ppt
Pd (Palladium)	≤ 50 ppt
Pr (Praseodymium)	≤ 20 ppt
Pt (Platinum)	≤ 50 ppt
Rb (Rubidium)	≤ 20 ppt
Re (Rhenium)	≤ 50 ppt
Rh (Rhodium)	≤ 50 ppt
Ru (Ruthenium)	≤ 50 ppt
Sb (Antimony)	≤ 50 ppt
Sc (Scandium)	≤ 20 ppt
Se (Selenium)	≤ 200 ppt
Sm (Samarium)	≤ 20 ppt
Sn (Tin)	≤ 50 ppt
Sr (Strontium)	≤ 50 ppt
Ta (Tantalum)	≤ 50 ppt
Tb (Terbium)	≤ 20 ppt
Te (Tellurium)	≤ 50 ppt
Th (Thorium)	≤ 10 ppt
Ti (Titanium)	≤ 50 ppt
Tl (Thallium)	≤ 50 ppt
Tm (Thulium)	≤ 20 ppt
U (Uranium)	≤ 10 ppt
V (Vanadium)	≤ 50 ppt
W (Tungsten)	≤ 100 ppt
Y (Yttrium)	≤ 10 ppt
Yb (Ytterbium)	≤ 20 ppt
Zn (Zinc)	≤ 500 ppt
Zr (Zirconium)	≤ 50 ppt

>>> Continued on page 3 >>>



Product Specification



Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

VWR International

