



## Sharpsafe® 4 Liter

SHA-41005430



Scalpel blade  
remover

Insulin pen  
remover



Luer-Slip

Luer-Lock

Unobstructed opening +  
Safety flap

### Features

- The container consists of two parts: a yellow body and translucent lid
- Safe, quick and simple 4 pressures assembly with 4 audible « click »
- Large « headroom » considered for the user as the safety area: 6 cm from the lid to the fill line
- Disconnection for all types of needle even for the scalpel blade and insulin pen
- Safety flap for extra protection (Option without Ref. : SHA-41006610\*)
- 2 closure positions on the flip top lid: temporary and final closure
- Reopening of the temporary closure with a simple finger pressure on the lid
- Possibility to block the lid in the open position
- Clearly visible fill line on the translucent lid
- In-mould label which cannot be removed, even by autoclaving
- Handle for a safe transport
- Can be used in a "single hand" way
- Accessories: Stands, hooks and brackets available
- Instruction of use on the label in French and Dutch (also available in English)
- Autoclaving valid to 135°C during 20 minutes for an empty and open container
- Conform to the NFX30-500 and BS7320 in terms of resistance to penetration, drop impact and liquid resistance. ADR and NF302 certificated. Holder of the brand NF302 (details see reverse)
- Origin of the product : European Union

SHA4L – 2010-10-EN-VWR

Manufactured by:

Marketed by:

Distributed by:



# Sharpsafe® 4 Liter

SHA-41005430








## Technical Information

- **Material:** Polypropylene
- **Max. nominal volume:** 4 L
- **Max. filling capacity:** 3 L
- **Dimensions opening:** 55 x 50 mm
- **Dimensions flip top closed:** 245 x 175 x 175 mm (HxLxW)
- **Weight:** 0,310 kg

## Packaging

- **Quantity per box:** 50
- **Dimensions box (HxLxW):** 417 x 843 x 355 mm
- **Weight:** 16,8 kg
- **Volume:** 0,125 m³
- **Box per pallet:** 14
- **Pallet dimensions:** 226 x 120 x 80 cm
- **Pallet weight:** 255 kg

## Conformity

|   |   |
|---|---|
|  | The NF-X-30-500 is the latest Sharps-guideline in Europe and the most rigorous European standard in terms of resistance to penetration, drop impact, perforation and liquid resistance  |
|  | The NF302 (Norme française) ensures the continued existence of the standards defined by NF-X-30-500. The „Laboratoire National d'Essais“ (French Institute for Standards) checks regularly the quality of the products on the market. |
|  | The British Standard BS 7320 sets rigorous standards in terms of resistance to penetration, drop impact, perforation and liquid resistance. The BS7320 is certificated via Kitemark.  |
|  | In conformity with A.D.R. and UN3291: International norm for the transport of dangerous material and infectious waste.  |
|  | The TRBA 250 is a German guideline for the treatment of biological, dangerous and infectious waste.   |
|  | Autoclave at 135°C during 20 min.   |
|  | Quality management system: ISO 9001:2008 and ISO 13485:2003<br>Environmental Standard: ISO 14001:2004   |

SHA4L – 2010-10-EN-VWR

Manufactured by:



Marketed by:



Distributed by:

