Certificate of Conformity

VWR TEST SIEVES, 300x60 mm

VWR International certifies that the products specified conform to all specifications and quality criteria mentioned in this document.

VWR International certifie que les produits mentionnés respectent toutes les specifications et critères de qualité mentionnés dans ce document.

VWR International bestätigt hiermit, daß die angegebenen Produkte alle in diesem Dokument erwähnten Spezifikationen und Qualitätskriterien erfüllen.

Catalog No.	Ø (mm)	Height (mm)	Mesh Size (mm)	Pk
510-2690	300 mm	60 mm	0,020 mm	1
510-2691	300 mm	60 mm	0,025 mm	1
510-2692	300 mm	60 mm	0,032 mm	1
510-2693	300 mm	60 mm	0,036 mm	1
510-2694	300 mm	60 mm	0,038 mm	1
510-2695	300 mm	60 mm	0,040 mm	1
510-2696	300 mm	60 mm	0,045 mm	1
510-2697	300 mm	60 mm	0,050 mm	1
510-2698	300 mm	60 mm	0,053 mm	1
510-2699	300 mm	60 mm	0,056 mm	1
510-2700	300 mm	60 mm	0,063 mm	1
510-2701	300 mm	60 mm	0,071 mm	1
510-2702	300 mm	60 mm	0,075 mm	1
510-2703	300 mm	60 mm	0,080 mm	1
510-2704	300 mm	60 mm	0,090 mm	1
510-2705	300 mm	60 mm	0,100 mm	1
510-2706	300 mm	60 mm	0,106 mm	1
510-2707	300 mm	60 mm	0,112 mm	1
510-2708	300 mm	60 mm	0,125 mm	1
510-2709	300 mm	60 mm	0,140 mm	1
510-2710	300 mm	60 mm	0,150 mm	1
510-2711	300 mm	60 mm	0,160 mm	1
510-2712	300 mm	60 mm	0,180 mm	1
510-2713	300 mm	60 mm	0,200 mm	1
510-2714	300 mm	60 mm	0,212 mm	1

Certificate of Conformity

Catalog No.	Ø (mm)	Height (mm)	Mesh Size (mm)	Pk
510-2715	300 mm	60 mm	0,224 mm	1
510-2716	300 mm	60 mm	0,250 mm	1
510-2717	300 mm	60 mm	0,280 mm	1
510-2718	300 mm	60 mm	0,300 mm	1
510-2719	300 mm	60 mm	0,315 mm	1
510-2720	300 mm	60 mm	0,315 mm	1
510-2721	300 mm	60 mm	0,400 mm	1
510-2722	300 mm	60 mm	0,425 mm	1
510-2723	300 mm	60 mm	0,450 mm	1
510-2724	300 mm	60 mm	0,500 mm	1
510-2725	300 mm	60 mm	0,560 mm	1
510-2726	300 mm	60 mm	0,600 mm	1
510-2727	300 mm	60 mm	0,630 mm	1
510-2728	300 mm	60 mm	0,710 mm	1
510-2729	300 mm	60 mm	0,800 mm	1
510-2730	300 mm	60 mm	0,850 mm	1
510-2731	300 mm	60 mm	0,900 mm	1
510-2732	300 mm	60 mm	1,00 mm	1
510-2733	300 mm	60 mm	1,12 mm	1
510-2734	300 mm	60 mm	1,18 mm	1
510-2735	300 mm	60 mm	1,25 mm	1
510-2736	300 mm	60 mm	1,40 mm	1
510-2737	300 mm	60 mm	1,60 mm	1
510-2738	300 mm	60 mm	1,70 mm	1
510-2739	300 mm	60 mm	1,80 mm	1
510-2739	300 mm	60 mm	1,80 mm	1
510-2740	300 mm	60 mm	2,00 mm	1
510-2741	300 mm	60 mm	2,24 mm	1
510-2742	300 mm	60 mm	2,36 mm	1
510-2743	300 mm	60 mm	2,50 mm	1
510-2744	300 mm	60 mm	2,80 mm	1
510-2745	300 mm	60 mm	3,15 mm	1
510-2746	300 mm	60 mm	3,35 mm	1
510-2747	300 mm	60 mm	3,55 mm	1

Certificate of Conformity

Catalog No.	Ø (mm)	Height (mm)	Mesh Size (mm)	Pk
510-2748	300 mm	60 mm	4,00 mm	1
510-2749	300 mm	60 mm	4,50 mm	1
510-2750	300 mm	60 mm	4,75 mm	1
510-2751	300 mm	60 mm	5,00 mm	1
510-2752	300 mm	60 mm	5,60 mm	1
510-2753	300 mm	60 mm	6,30 mm	1
510-2754	300 mm	60 mm	6,70 mm	1
510-2755	300 mm	60 mm	7,10 mm	1
510-2756	300 mm	60 mm	8,00 mm	1
510-2757	300 mm	60 mm	9,00 mm	1
510-2758	300 mm	60 mm	9,50 mm	1
510-2759	300 mm	60 mm	10,00 mm	1
510-2760	300 mm	60 mm	11,20 mm	1
510-2761	300 mm	60 mm	12,50 mm	1
510-2762	300 mm	60 mm	13,20 mm	1
510-2763	300 mm	60 mm	14,00 mm	1
510-2764	300 mm	60 mm	16,00 mm	1
510-2765	300 mm	60 mm	18,00 mm	1
510-2766	300 mm	60 mm	19,00 mm	1
510-2767	300 mm	60 mm	20,00 mm	1
510-2768	300 mm	60 mm	22,40 mm	1
510-2769	300 mm	60 mm	25,00 mm	1
510-2770	300 mm	60 mm	26,50 mm	1
510-2771	300 mm	60 mm	28,00 mm	1
510-2772	300 mm	60 mm	31,50 mm	1
510-2773	300 mm	60 mm	35,50 mm	1
510-2774	300 mm	60 mm	37,50 mm	1
510-2775	300 mm	60 mm	40,00 mm	1
510-2776	300 mm	60 mm	45,00 mm	1
510-2777	300 mm	60 mm	50,00 mm	1
510-2778	300 mm	60 mm	53,00 mm	1
510-2779	300 mm	60 mm	56,00 mm	1
510-2780	300 mm	60 mm	63,00 mm	1
510-2781	300 mm	60 mm	71,00 mm	1

Certificate of Conformity

Catalog No.	Ø (mm)	Height (mm)	Mesh Size (mm)	Pk
510-2782	300 mm	60 mm	75,00 mm	1
510-2783	300 mm	60 mm	80,00 mm	1
510-2784	300 mm	60 mm	90,00 mm	1
510-2785	300 mm	60 mm	100,00 mm	1
510-2786	300 mm	60 mm	106,00 mm	1
510-2787	300 mm	60 mm	112,00 mm	1
510-2788	300 mm	60 mm	125,00 mm	1

Material
Frame and Tension ring = AISI 304 (1.4301)
Test Sieve Cloth = AISI 316 (1.4401) for Mesh sizes 0.020 – 2.50 mm
Test Sieve Cloth = AISI 316 (1.4301) for Mesh sizes 2.80 – 125 mm

Compliance

- In compliance to DIN ISO 3310-1, ISO 3310-1, ASTM E11, BS ISO 3310-1
- Maintenance of Test Sieve is in compliance to ISO 2591-1, DIN 66165

Disclaimer: *VWR wants to state that this declaration will not discharge the user from his obligation to ensure the product is suitable for the intended use. - If there is any doubt ask us.*

Date of issue: **November 2017**