



Instructions for use

GrowDase™

CONTENTS

1. Safety information
2. Product storage instructions
3. GrowDase™ is used for the enzymatic degradation of GrowDex®
4. Procedure for removing GrowDex® by enzymatic degradation
5. Example experimental procedure
6. Dilution table
7. Ordering information
8. Contact information

This product is intended for research use only and should not be used for diagnostic or therapeutic purposes

1. SAFETY INFORMATION

GrowDase™ consists of a cellulase enzyme mixture in aqueous sodium acetate buffer solution, pH 5. The product is sterile and intended for the degradation of GrowDex®. GrowDase™ is for research use only, not for diagnostic or therapeutic use.

In accordance with current regulations (1272/2008 CLP), this substance has not been classified as dangerous. The product contains up to 10 mg/ml enzymes. The product has been sterile filtered.

The product should be handled in accordance with good industrial hygiene and safety practices. Use protective gloves and clothes to avoid skin exposure. If exposed wash the skin with water. Use protective laboratory eye wear to avoid contact with the eyes.

Hazard Statements:

H317: May cause an allergic reaction.

Description of first aid measures

- Inhalation: Move to fresh air. Seek medical attention if symptoms appear.
- Skin contact: Wash with water. Seek medical attention if irritation occurs.
- Eye contact: Rinse with plenty of water for several minutes. Seek medical attention if irritation occurs.
- Ingestion: Rinse mouth with plenty of water. If large quantities of the product are ingested endeavour to vomit. Seek medical attention if symptoms appear.

Most important symptoms and effects, both acute and delayed

- Inhalation: May produce an allergic reaction.
- Ingestion: No symptoms or effects known.
- Skin contact: No symptoms or effects known.
- Eye contact: No symptoms or effects known.

NOTE: For further information refer to the GrowDase™ Material Safety Data Sheet

2. PRODUCT STORAGE INSTRUCTIONS

The unopened product has a shelf life of 6 months from date of manufacture and should be stored in the dark at 5-22°C (41-71°F) for optimum performance.

Once opened it is recommended that the product is stored at 2-8°C for a maximum of 6 months.

If the product has been diluted, e.g. with culture media, then it should be used immediately. Any leftover diluted enzyme should be discarded.

3. GROWDASE™ IS USED FOR THE ENZYMATIC DEGRADATION OF GROWDEX®

GrowDase™ is a purified mixture of cellulase enzymes that has been specifically developed to reduce the nano-cellulose fibrils present in GrowDex® to soluble glucose.

The process is simple, enzyme is mixed with the sample and incubated at 37°C until the GrowDex® has been fully reduced to glucose.

Enzymatic removal allows cells to be recovered from the matrix efficiently, retain their 3D structure, e.g. spheroid or organoid intact and without adverse affect on cell functionality.


The amount of GrowDase™ required for cell recovery is dependent on the amount of GrowDex® (cellulose) present in the sample.

It is recommended that GrowDase™ is used at a working concentration of 300 µg/mg. An equal volume of working concentration GrowDase™ to GrowDex®/cell matrix volume present in the sample should be used, i.e. if 100 µl of GrowDex®/cell matrix is present in the sample then 100 µl of GrowDase™ (300 µg/mg) should be added to that sample well.

Spheroids cultured in
GrowDex®

GrowDase™ added, sample
incubated at 37°C

GrowDex® degraded
to glucose, spheroids
are in solution



4. PROCEDURE FOR REMOVING GROWDEX® BY ENZYMATIC DEGRADATION

- a) Calculate the amount of GrowDex® present in the sample well using the following equation:
NOTE: 100 µl of 1 % GrowDex® = 1 mg
Sample well volume (µl) x % GrowDex® concentration / 100 = mg GrowDex® / sample well
- b) Calculate the amount enzyme needed to degrade the GrowDex® in the sample well using the following equation:
NOTE: 300 µg GrowDase™ enzyme is required to degrade 1 mg of GrowDex®
Number (mg) GrowDex®/sample well x 300 = µg GrowDase™ enzyme
- c) Calculate the volume of GrowDase™ stock solution needed using the following equation:
GrowDase™ amount (µg) / GrowDase™ stock concentration (10ug/µl) = Volume (µl) of GrowDase™ stock solution
- d) Prepare the working concentration of GrowDase™ by diluting the stock solution with culture media as follows:
Sample well volume (µl) - Volume (µl) of GrowDase™ stock solution (10 mg/ml) = Volume of culture media for dilution
- e) Pipette the diluted GrowDase™ onto the top of the sample in the microplate.
- f) Incubate the plate at 37°C for a minimum of 8 hours until the hydrogel has fully degraded.
- g) Recover the cells from the well using standard techniques.

5. EXAMPLE EXPERIMENTAL PROCEDURE

- SAMPLE:** 80 µl of 0.9 % GrowDex®/cell mix per well in a 96-well microplate
- MATERIALS**
- GrowDase™ enzyme, 10 mg/ml (10 µg/ µl)
 - Cell culture medium
- METHOD**
- a) Amount of GrowDex® present in the sample:
80 µl x 0.9 / 100 = 0.72 mg GrowDex® / sample well
- b) Amount of GrowDase™ needed to degrade the GrowDex® in the sample :
0.72 mg x 300 µg/mg = 216 µg GrowDase™ enzyme
- c) Volume of GrowDase™ stock solution needed:
216 µl / 10 µg/µl = 21.6 µl GrowDase™ enzyme stock solution
- d) Prepare the working concentration of GrowDase™ by diluting the stock solution (10 mg/ml) with culture media:
80 µl - 21.6 µl = 58.4 µl culture media for dilution
- e) Pipette the diluted GrowDase™ onto the top of the sample in the microplate.
- f) Incubate the plate at 37°C until the hydrogel has fully degraded.
- g) Recover the cells from the well using standard techniques.

6. DILUTION TABLE

Volume of GrowDase™ enzyme and cell culture medium required for the preparation of 100 µl of GrowDase™ working solution (300 µg/mg) for the degradation of 100 µl of GrowDex®.

| GROWDEX® CONCENTRATION IN 100 µl OF SAMPLE | AMOUNT OF GROWDASE™ ENZYME NEEDED | VOLUME OF GROWDASE™ ENZYME STOCK SOLUTION (10 mg/ml) | VOLUME OF CELL CULTURE MEDIUM |
|--|-----------------------------------|--|-------------------------------|
| 1 % | 300 µg | 30 µl | 70 µl |
| 0.9 % | 270 µg | 27 µl | 73 µl |
| 0.8 % | 240 µg | 24 µl | 76 µl |
| 0.7 % | 210 µg | 21 µl | 79 µl |
| 0.6 % | 180 µg | 18 µl | 82 µl |
| 0.5 % | 150 µg | 15 µl | 85 µl |
| 0.4 % | 120 µg | 12 µl | 88 µl |
| 0.3 % | 90 µg | 9 µl | 91 µl |

7. ORDERING INFORMATION

| CATALOGUE CODE | DESCRIPTION |
|----------------|------------------------------------|
| 100 100 005 | 5 ml GrowDex® 1.5 %, plastic vial |
| 100 100 010 | 10 ml GrowDex® 1.5 %, plastic vial |
| 100 102 005 | 5 ml GrowDex® 1.5 %, glass vial |
| 100 102 010 | 10 ml GrowDex® 1.5 %, glass vial |
| 900 102 002 | 2,5 ml GrowDase™ 10 mg/ml |

You can order via our website using the online order form found at: www.growdex.com

Or contact us at growdex.sales@upm.com for a quotation or to place an order.

8. CONTACT INFORMATION

- Additional information on all products and applications can be found on our website visit: www.growdex.com
- Should you have any questions or queries regarding this product or its intended use please contact us at:
- EMAIL:** growdex.support@upm.com
- POST:** UPM Biochemicals
Alvar Aallon katu 1
P.O. Box 380
00101 Helsinki
Finland
- TEL:** +358 (0)204 15 111 and request to speak with one of the GrowDex® team
- FAX:** +358 (0)204 15 110