Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

Revision date: 21.10.2020	*Version: 7.2*	*Print date: 21.10.2020*

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name/designation:	Triethylamine HiPerSolv CHROMANORM® for HPLC
Product No.:	28757
CAS No.:	121-44-8
Index No.:	612-004-00-5
REACH No.:	01-2119475467-26-XXXX
Other means of identification:	(Diethylamino)ethane, TEA

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses:	General chemical reagent

1.3 Details of the supplier of the safety data sheet

United Kingdom

VWR International Ltd.

Street	Hunter Boulevard, Magna Park
Postal code/City	Lutterworth, LE17 4XN
Telephone	0800 22 33 44
Telefax:	01455 55 85 86
E-mail (competent person)	SDS@vwr.com

1.4 Emergency phone number

Telephone	+44 (0) 1270 502894 (CareChem24)

SECTION 2: Hazard identification

2.1 Classification of the substance or mixture

2.1.1 Classification according to Regulation (EC) No 1272/2008 [CLP]

Hazard classes and hazard categories	Hazard statements
Flammable liquid, category 2	H225
Acute toxicity, category 3, dermal and inhalation	H311+H331
Acute toxicity, category 4, oral	H302
Skin corrosion, category 1A	H314
Serious eye damage, category 1	H318
Specific target organ toxicity (single exposure), category 3, vascular	H335

2.2 Label elements

2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms



Signal word: Danger

Hazard statements	
H225	Highly flammable liquid and vapour.
H311+H331	Toxic in contact with skin or if inhaled.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H335	May cause respiratory irritation.

Precautionary statements	
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P303+P361+P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+P310	IF exposed or concerned: Immediately call a POISON CENTER/doctor.

2.3 Other hazards

This substance does not meet the PBT/vPvB criteria of REACH, Annex XIII.

SECTION 3: Composition / information on ingredients

3.1 Substances

Substance name	Triethylamine
Molecular formula	$(C_2H_5)_3N$
Molecular weight	101.19 g/mol
CAS No.	121-44-8
REACH registration No.	01-2119475467-26-XXXX
Index No.	612-004-00-5

SECTION 4: First aid measures

4.1 General information

IF exposed: Immediately call a POISON CENTRE/doctor. If unconscious but breathing normally, place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

After inhalation

Immediately call a POISON CENTRE/doctor. Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. Immediate medical treatment required because corrosive injuries that are not treated are hard to cure.

After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

In case of ingestion

Immediately call a POISON CENTRE/doctor. Do NOT induce vomiting. Rinse mouth thoroughly with water. Give nothing to eat or drink.

Self-protection of the first aider

First aider: Pay attention to self-protection!

4.2 Most important symptoms and effects, both acute and delayed

no data available

4.3 Indication of any immediate medical attention and special treatment needed

no data available

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Water spray
ABC-powder

Carbon dioxide (CO2)
Nitrogen

Extinguishing media which must not be used for safety reasons
no restriction

5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated:
Carbon monoxide
Carbon dioxide (CO2)
Nitrogen oxides (NOx)

5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives.
Special protective equipment for firefighters
Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Do not allow run-off from fire-fighting to enter drains or water courses.
Do not inhale explosion and combustion gases.
Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen.
Use water spray jet to protect personnel and to cool endangered containers.
In case of fire: Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety.

6.2 Environmental precautions

Discharge into the environment must be avoided.

6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Collect in closed and suitable containers for disposal.

6.4 Additional information

Clear spills immediately.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Avoid:
Inhalation
Avoid contact with eyes and skin.
Use extractor hood (laboratory).
If handled uncovered, arrangements with local exhaust ventilation have to be used.
If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.
Keep away from sources of ignition - No smoking.
Usual measures for fire prevention.
Take precautionary measures against static discharges.
May cause decomposition by long-term light influence.
Protect from moisture.

7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: 15-25°C
Storage class: 3
Keep container tightly closed and in a well-ventilated place. Always close containers tightly after the removal of product.

7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredient (Designation)	Regulatory information	Country	Limit value type (country of origin)	Limit value	Remark
Triethylamine	2000/39/EC	EU	LTV	8.4 mg/m³ - 2 ppm	
Triethylamine	2000/39/EC	EU	STV	12.6 mg/m³ - 3 ppm	

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

8.2.2 Personal protection equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn.

Eye/face protection

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166
Recommendation: VWR 111-0432

Skin protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms EN ISO 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.

By short-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,12 mm
Breakthrough time::	155 min
Recommended glove articles:	VWR 112-0998

By long-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,38 mm
Breakthrough time::	> 480 min
Recommended glove articles:	VWR 112-3717 / 112-1381

Respiratory protection

Respiratory protection necessary at: aerosol or mist formation

Suitable respiratory protection apparatus:	Full-/half-/quarter-face masks (DIN EN 136/140)
Recommendation:	VWR 111-0206
Suitable material:	ABEK2P3
Recommendation:	VWR 111-0059

Additional information

Wash hands before breaks and after work. Avoid contact with eyes and skin. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

8.2.3 *Environmental exposure controls*

no data available

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	liquid
Colour:	colourless
(b) Odour:	no data available
(c) Odour threshold:	no data available

Safety relevant basic data

(d) pH:	12-13 (100 g/l; H2O; 15 °C)
(e) Melting point/freezing point:	-115 °C
(f) Initial boiling point and boiling range:	90 °C (1013 hPa)
(g) Flash point:	-11 °C
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	Highly flammable liquid and vapour.
(j) Flammability or explosive limits	
Lower explosion limit:	1.2 % (v/v)
Upper explosion limit:	9.3 % (v/v)
(k) Vapour pressure:	69 hPa (20 °C)
(l) Vapour density:	3.5 (20 °C)
(m) Relative density:	0.729 g/cm³ (20 °C)
(n) Solubility(ies)	
Water solubility:	133 g/l (20 °C)
Soluble (g/L) in Ethanol:	no data available
(o) Partition coefficient: n-octanol/water:	1.45 (20 °C)
(p) Auto-ignition temperature:	215 °C
(q) Decomposition temperature:	no data available
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	0.36 mPa*s (20 °C)
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable

9.2 Other information

Bulk density:	no data available
Refraction index:	1.4003 (589 nm; 20 °C)
Dissociation constant:	no data available
Surface tension:	no data available
Henry's Law Constant:	no data available

SECTION 10: Stability and reactivity

10.1 Reactivity

no data available

10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

no data available

10.6 Hazardous decomposition products

no data available

10.7 Additional information

no data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:
LD50: 730 mg/kg - Rat - (Gestis)

Acute dermal toxicity:
LD50: 580 mg/kg - Rabbit - (Gestis)

Acute inhalation toxicity:
LC50: 7220 mg/m3 (4h) - Rat - (OECD 403)

Irritant and corrosive effects

Primary irritation to the skin:
Causes severe skin burns and eye damage.

Irritation to eyes:
Causes serious eye damage.

Irritation to respiratory tract:
May cause respiratory irritation.

Respiratory or skin sensitisation
In case of skin contact: not sensitising
After inhalation: not sensitising

STOT-single exposure
May cause respiratory irritation.

STOT-repeated exposure
not applicable

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)
Carcinogenicity
No indication of human carcinogenicity.

Germ cell mutagenicity
No indications of human germ cell mutagenicity exist.

Reproductive toxicity
No indications of human reproductive toxicity exist.

Aspiration hazard
not applicable

Other adverse effects
no data available

Additional information
no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Fish toxicity:
no data available

Daphnia toxicity:
no data available

Algae toxicity:
no data available

Bacteria toxicity:
no data available

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: 1.45 (20 °C)

12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

This substance does not meet the PBT/vPvB criteria of REACH, Annex XIII.

12.6 Other adverse effects

no data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Appropriate disposal / Product

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal. Send to a hazardous waste incinerator facility under observation of official regulations.

Waste code product: 061002

Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

Additional information

no data available

SECTION 14: Transport information

Land transport (ADR/RID)

14.1	UN-No.:	1296
14.2	Proper Shipping Name:	TRIETHYLAMINE
14.3	Class(es):	3 (8)
	Classification code:	FC
	Hazard label(s):	3+8
14.4	Packing group:	II
14.5	Environmental hazards:	No
14.6	Special precautions for user:	
	Hazard identification number (Kemler No.):	338
	tunnel restriction code:	D/E (Passage forbidden through tunnels of category D when carried in bulk or in tanks. Passage forbidden through tunnels of category E.)

Sea transport (IMDG)

14.1	UN-No.:	1296
14.2	Proper Shipping Name:	TRIETHYLAMINE
14.3	Class(es):	3 (8)
	Classification code:	
	Hazard label(s):	3+8

14.4	Packing group:	II
14.5	Environmental hazards:	No
	Marine pollutant:	No
14.6	Special precautions for user:	
	Segregation group:	-
	EmS-No.	F-E S-C
14.7	Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	
	not relevant	

Air transport (ICAO-TI / IATA-DGR)

14.1	UN-No.:	1296
14.2	Proper Shipping Name:	TRIETHYLAMINE
14.3	Class(es):	3 (8)
	Classification code:	
	Hazard label(s):	3+8
14.4	Packing group:	II
14.5	Special precautions for user:	

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

- Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC (Text with EEA relevance)
- Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 (Text with EEA relevance)
- Commission Regulation (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (Text with EEA relevance)
- Commission Regulation (EU) 2015/830 of 28 May 2015 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)

National regulations

no data available

Water hazard class: slightly hazardous to water

15.2 Chemical Safety Assessment

For this substance a chemical safety assessment has not been carried out.

SECTION 16: Other information

Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygiensts
ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road
AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)
CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures
DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)
Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)
IATA-DGR - International Air Transport Association-Dangerous Goods Regulations
ICAO-TI - International Civil Aviation Organization-Technical Instructions
IMDG - International Maritime Code for Dangerous Goods
LTV - Long Term Value
NIOSH - National Institute for Occupational Safety and Health
OSHA - Occupational Safety & Health Administration
PBT - Persistent, Bioaccumulative and Toxic
RID - Regulation concerning the International Carriage of Dangerous Goods by Rail
STV - Short Term Value
SVHC - Substances of Very High Concern
vPvB - very Persistent, very Bioaccumulative

Training advice: Provide adequate information, instruction and training for operators.

Additional information

Indication of changes	Section 2 If you need an explanation of the change, contact the supplier. (SDS@avantorsciences.com)

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.