

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

Revision date: 25.08.2022

Version: 7.3

Print date: 25.08.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name/designation:	Methanol PESTINORM® for pesticide residue analysis
Product No.:	83662
CAS No.:	67-56-1
Index No.:	603-001-00-X
EU REACH No.:	01-2119433307-44-XXXX
Other means of identification:	Carbinol, Hydroxy methane, Methyl alcohol, Wood alcohol

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses:	General chemical reagent
---------------------------	--------------------------

1.3 Details of the supplier of the safety data sheet

United Kingdom

VWR International Ltd.

Street	Hunter Boulevard, Magna Park
Postal code/City	Lutterworth, LE17 4XN
Telephone	0800 22 33 44
Telefax	01455 55 85 86
E-mail (competent person)	SDS@avantorsciences.com

1.4 Emergency phone number

Telephone	+44 (0) 1270 502894 (CareChem24)
-----------	----------------------------------

SECTION 2: Hazard identification

2.1 Classification of the substance or mixture

2.1.1 Classification according to Regulation (EC) No 1272/2008 [CLP]

Hazard classes and hazard categories	Hazard statements
Flammable liquid, category 2	H225
Specific target organ toxicity (single exposure), category 1	H370
Acute toxicity, category 3, oral, dermal and inhalation	H301+H311+H331

2.2 Label elements

2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms



Signal word: Danger

Hazard statements	
H225	Highly flammable liquid and vapour.
H301+H311+H331	Toxic if swallowed, in contact with skin or if inhaled.
H370	Causes damage to organs.

Precautionary statements	
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P243	Take precautionary measures against static discharge.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P302+P352	IF ON SKIN: Wash with plenty of water/...
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P308+P310	IF exposed or concerned: Immediately call a POISON CENTER/doctor.

2.3 Other hazards

This substance does not meet the PBT/vPvB criteria of REACH, Annex XIII.

SECTION 3: Composition / information on ingredients

3.1 Substances

Substance name: Methanol
Molecular formula: H₃COH

Molecular weight:	32.04 g/mol
CAS No.:	67-56-1
EU REACH registration No.:	01-2119433307-44-XXXX
EC No.:	200-659-6
ATE, SCL and/or M-factor:	*
	STOT SE 1; H370: C ≥ 10 %
	STOT SE 2; H371: 3 % ≤ C < 10 %

SECTION 4: First aid measures

4.1 Description of first aid measures

General information

IF exposed: Immediately call a POISON CENTRE/doctor. If unconscious but breathing normally, place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

After inhalation

Immediately call a POISON CENTRE/doctor. Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

After eye contact:

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

In case of ingestion

Immediately call a POISON CENTRE/doctor. Do NOT induce vomiting. Rinse mouth thoroughly with water. Give nothing to eat or drink.

Self-protection of the first aider

First aider: Pay attention to self-protection!

4.2 Most important symptoms and effects, both acute and delayed

Headache. Dizziness. Nausea. Respiratory disorders. Coma. Acidosis Risk of blindness.

4.3 Indication of any immediate medical attention and special treatment needed

Treat symptomatically. Following ingestion: Administer 50 ml of pure ethanol in a drinkable concentration.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Water spray
ABC-powder

Carbon dioxide (CO₂)
Nitrogen

Extinguishing media which must not be used for safety reasons

Full water jet

5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated:

Carbon monoxide
Carbon dioxide (CO₂)

5.3 Advice for firefighters

In case of fire and/or explosion do not breathe fumes.

In case of insufficient ventilation and/or through use, explosive/highly flammable mixtures may develop.

Vapours are heavier than air, spread along floors and form explosive mixtures with air.

Special protective equipment for firefighters:

Wear a self-contained breathing apparatus and chemical protective clothing.

Use water spray jet to protect personnel and to cool endangered containers.

DO NOT fight fire when fire reaches explosives.

Additional information

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen.

Use water spray jet to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Avoid contact with skin, eyes and clothes. Avoid inhalation of the product. Take off immediately all contaminated clothing.

6.2 Environmental precautions

Discharge into the environment must be avoided. Do not allow to enter into surface water or drains. Explosion risk.

6.3 Methods and material for containment and cleaning up

Absorb with liquid-binding material (sand, diatomaceous earth, acid- or universal binding agents). Collect in closed and suitable containers for disposal. Ventilate affected area.

6.4 Additional information

Clear spills immediately.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Avoid inhalation of the product.

Avoid contact with eyes and skin.

Wear protective gloves/protective clothing and eye/face protection.

Use extractor hood (laboratory).

If handled uncovered, arrangements with local exhaust ventilation have to be used.

If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

Take precautionary measures against static discharges.

Usual measures for fire prevention.

Due to danger of explosion, prevent leakage of vapours into cellars, flues and ditches.

Wash hands before breaks and after work. Avoid contact with eyes and skin. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: 15-25°C

Storage class: 3

Keep container tightly closed and in a well-ventilated place. Keep cool. Protect from sunlight. Store in a place accessible by authorized persons only. Keep/Store away from combustible materials. Ground and bond container and receiving equipment.

Provide adequate ventilation.

7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredient (Designation)	Regulatory information	Country	Limit value type (country of origin)	Limit value	Remark
Methanol	DNEL	EU	Worker, Dermal, long-term, systemic	20 mg/kg bw/day	
Methanol	DNEL	EU	Worker, Dermal, short-term, systemic	20 mg/kg bw/day	
Methanol	DNEL	EU	Worker, Inhalation, long-term, local	130 mg/m ³	
Methanol	DNEL	EU	Worker, Inhalation, long-term, systemic	130 mg/m ³	
Methanol	DNEL	EU	Worker, Inhalation, short-term, local	130 mg/m ³	
Methanol	DNEL	EU	Worker, Inhalation, short-term, systemic	130 mg/m ³	
Methanol	Directive 98/24/EC	EU	LTV	260 mg/m ³ - 200 ppm	Skin Designation
Methanol	EH40/2005 - Fourth Edition 2020	UK	LTV	266 mg/m ³ - 200 ppm	
Methanol	EH40/2005 - Fourth Edition 2020	UK	STV	333 mg/m ³ - 250 ppm	

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

8.2.2 Personal protection equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn.

Eye/face protection

Eye glasses with side protection DIN-/EN-Norms DIN EN 166

Recommendation: VWR 111-0432

Skin protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms EN ISO 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.

By short-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,38 mm
Breakthrough time::	-
Recommended glove articles:	VWR 112-1381

By long-term hand contact

Suitable material:	Butyl caoutchouc (butyl rubber)
Thickness of the glove material:	0,30 mm
Breakthrough time::	> 480 min
Recommended glove articles:	VWR 112-3779

Respiratory protection

Respiratory protection necessary at: aerosol or mist formation

Suitable respiratory protection apparatus:	Full-/half-/quarter-face masks (DIN EN 136/140)
Recommendation:	VWR 111-0206
Suitable material:	AXP3
Recommendation:	VWR 111-8932

Additional information

Wash hands before breaks and after work. Avoid contact with eyes and skin. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

8.2.3 *Environmental exposure controls*
no data available

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	liquid
Colour:	colourless
(b) Odour:	characteristic
(c) Odour threshold:	no data available

Safety relevant basic data

(d) pH:	7 (20 °C)
(e) Melting point/freezing point:	-98 °C
(f) Initial boiling point and boiling range:	64.6 °C (1013 hPa)
(g) Flash point:	11 °C (closed cup)
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	Highly flammable liquid and vapour.
(j) Flammability or explosive limits	
Lower explosion limit:	5.5 % (v/v)
Upper explosion limit:	36.5 % (v/v)
(k) Vapour pressure:	128 hPa (20 °C)
(l) Vapour density:	1.11 (20 °C)
(m) Density:	0.7918 g/cm ³ (20 °C)
(n) Solubility(ies)	
Water solubility:	soluble (20 °C)
(o) Partition coefficient: n-octanol/water:	-0.77 (20 °C)
(p) Auto-ignition temperature:	455 °C (DIN 51794)
(q) Decomposition temperature:	not applicable
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	0.614 mPa*s (20 °C)
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable
(u) Particle characteristics:	does not apply to liquids

9.2 Other information

Bulk density:	no data available
Refraction index:	1.33066 (589 nm; 20 °C)
Dissociation constant:	no data available
Surface tension:	no data available
Henry's Law Constant:	no data available

SECTION 10: Stability and reactivity

10.1 Reactivity

This material is non-reactive under normal conditions.

Chemical stability

Vapour can form explosive mixtures with air.

10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

10.3 Possibility of hazardous reactions

Formation of explosive mixtures with:

Oxidising agent

Nitrogen oxides (NO_x)

Chlorates

Nitric acid

Sulphuric acid.

Exothermic reaction with:

Reducing agent

Acid

Acid halides

Alkali (lye), concentrated

Violent reaction with:

Alkali metals

Alkaline earth metal

Formation of:

Hydrogen

10.4 Conditions to avoid

UV-radiation/sunlight

Heat

Sparks.

Flame

10.5 Incompatible materials

Acids

Alkali metals

Oxidising agent

10.6 Hazardous decomposition products

Formaldehyde

10.7 Additional information

Slowly corrodes aluminium and zinc under hydrogen evolution.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:

LDLo: > 143 mg/kg - Human - (RTECS)

LD50: 1187 - 2769 mg/kg - Rat - (IUCLID)

LD50: 1187 - 2769 mg/kg - Rat - (OECD 401)

Acute dermal toxicity:

LD50: > 15800 mg/kg - Rabbit

LD50: 17100 mg/kg - Rabbit - (ECHA)

Acute inhalation toxicity:

TCLo: > 160 ppm (4 h) - Human

LD50: 43700 mg/m³ (6 h) - Cat - (J Appl Toxicol 14(4): 309-313)

Irritant and corrosive effects

Primary irritation to the skin:

not applicable

Irritation to eyes:

not applicable

Irritation to respiratory tract:

not applicable

Respiratory or skin sensitisation

In case of skin contact: not sensitising

After inhalation: not sensitising

STOT-single exposure

Causes damage to organs.

STOT-repeated exposure

not applicable

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Carcinogenicity

No indication of human carcinogenicity.

Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.

Reproductive toxicity

No indications of human reproductive toxicity exist.

Aspiration hazard

not applicable

Other adverse effects

no data available

Additional information

no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Fish toxicity:

LC50: 24000 mg/l (96 h) - Poirier, S.H., M.L. Knuth, C.D. Anderson-Buchou, L.T. Brooke, A.R. Lima, and P.J. Shubat 1986. Comparative Toxicity of Methanol and N,N-Dimethylformamide to Freshwater Fish and Invertebrates. Bull.Environ.Contam.Toxicol. 37(4):615-621

Daphnia toxicity:

LC50: 3290 mg/l (48 h) - Guilhermino, L., T. Diamantino, M.C. Silva, and A.M.V.M. Soares 2000. Acute Toxicity Test with Daphnia magna: An Alternative to Mammals in the Prescreening of Chemical Toxicity?. Ecotoxicol.Environ.Saf. 46(3):357-362

EC50: 24500 mg/l (48 h) - Randall, T.L., and P.V. Knopp 1980. Detoxification of Specific Organic Substances by Wet Oxidation. J.Water Pollut.Control Fed. 52(8):2117-2130

Algae toxicity:

EC50: 22 000 mg/l (96 h) Pseudokirchneriella subcapitata - IUCLID

Bacteria toxicity:

no data available

12.2 Persistence and degradability

Biodegradable.

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: -0.77 (20 °C)

12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

This substance does not meet the PBT/vPvB criteria of REACH, Annex XIII.

12.6 Other adverse effects

no data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Appropriate disposal / Product

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: 070104

Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

Additional information

no data available

SECTION 14: Transport information

Land transport (ADR/RID)

14.1	UN-No.:	1230
14.2	Proper Shipping Name:	METHANOL
14.3	Class(es):	3 (6.1)
	Classification code:	FT1
	Hazard label(s):	3+6.1
14.4	Packing group:	II
14.5	Environmental hazards:	No
14.6	Special precautions for user:	
	Hazard identification number (Kemler No.):	336
	tunnel restriction code:	D/E
		(Passage forbidden through tunnels of category D when carried in bulk or in tanks. Passage forbidden through tunnels of category E.)

Sea transport (IMDG)

14.1	UN-No.:	1230
14.2	Proper Shipping Name:	METHANOL
14.3	Class(es):	3 (6.1)
	Classification code:	
	Hazard label(s):	3+6.1
14.4	Packing group:	II
14.5	Environmental hazards:	No
	Marine pollutant:	No
14.6	Special precautions for user:	
	Segregation group:	-
	EmS-No.	F-E S-D
14.7	Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	
	not relevant	

Air transport (ICAO-TI / IATA-DGR)

14.1	UN-No.:	1230
14.2	Proper Shipping Name:	METHANOL
14.3	Class(es):	3 (6.1)
	Classification code:	
	Hazard label(s):	3+6.1
14.4	Packing group:	II
14.5	Special precautions for user:	

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

- Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC (Text with EEA relevance)
- Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 (Text with EEA relevance)
- Commission Regulation (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (Text with EEA relevance)
- Commission Regulation (EU) 2015/830 of 28 May 2015 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)

Use restriction according to REACH annex XVII, no.: 69

National regulations

-

Water hazard class: slightly hazardous to water

15.2 Chemical Safety Assessment

For this substance a chemical safety assessment has not been carried out.

SECTION 16: Other information

Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists
ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road
AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)
CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures
DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)
DNEL - Derived No Effect Level
Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)
IATA-DGR - International Air Transport Association-Dangerous Goods Regulations
ICAO-TI - International Civil Aviation Organization-Technical Instructions
IMDG - International Maritime Code for Dangerous Goods
KOSHA - Korea Occupational Safety and Health Agency
LTV - Long Term Value
NIOSH - National Institute for Occupational Safety and Health
OSHA - Occupational Safety & Health Administration
PBT - Persistent, Bioaccumulative and Toxic
PNEC - Predicted No Effect Concentration
RID - Regulation concerning the International Carriage of Dangerous Goods by Rail
STV - Short Term Value
SVHC - Substances of Very High Concern
vPvB - very Persistent, very Bioaccumulative

Training advice: Provide adequate information, instruction and training for operators.

Key literature references and sources for data

This Safety Data Sheet has been prepared based on information available for public as TOXNET information, European Chemicals Agency (ECHA) substance dossier, papers from international cancer research institutes (IARC Monographs), U.S. National Toxicology Program data, U.S. Agency for Toxic Substances and Disease Control (ATSDR), PubChem websites and SDS from our raw material manufacturers.

Additional information

Indication of changes Section 8: Update of DNEL and/or PNEC data

If you need an explanation of the change, contact the supplier (SDS@avantorsciences.com).

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.