

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

Revision date: 31.07.2020

Version: 7.2

Print date: 31.07.2020

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

| | |
|--------------------------------|----------------------------------|
| Trade name/designation: | Chloroform HiPerSolv CHROMANORM® |
| Product No.: | 83627 |
| CAS No.: | 67-66-3 |
| Index No.: | 602-006-00-4 |
| REACH No.: | 01-2119486657-20-XXXX |
| Other means of identification: | none |

1.2 Relevant identified uses of the substance or mixture and uses advised against

| | |
|---------------------------|--------------------------|
| Relevant identified uses: | General chemical reagent |
|---------------------------|--------------------------|

1.3 Details of the supplier of the safety data sheet

United Kingdom

VWR International Ltd.

| | |
|---------------------------|------------------------------|
| Street | Hunter Boulevard, Magna Park |
| Postal code/City | Lutterworth, LE17 4XN |
| Telephone | 0800 22 33 44 |
| Telefax: | 01455 55 85 86 |
| E-mail (competent person) | SDS@vwr.com |

1.4 Emergency phone number

| | |
|-----------|----------------------------------|
| Telephone | +44 (0) 1270 502894 (CareChem24) |
|-----------|----------------------------------|



SECTION 2: Hazard identification

2.1 Classification of the substance or mixture

2.1.1 Classification according to Regulation (EC) No 1272/2008 [CLP]

| Hazard classes and hazard categories | Hazard statements |
|--|-------------------|
| Acute toxicity, category 3, inhalation | H331 |
| Acute toxicity, category 4, oral | H302 |
| Skin irritation, category 2 | H315 |
| Eye irritation, category 2 | H319 |
| Carcinogenicity, category 2 | H351 |
| Reproductive toxicity, category 2 | H361d |
| Specific target organ toxicity (repeated exposure), category 1 | H372 |

2.2 Label elements

2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms



Signal word: Danger

| Hazard statements | |
|-------------------|---|
| H331 | Toxic if inhaled. |
| H302 | Harmful if swallowed. |
| H315 | Causes skin irritation. |
| H319 | Causes serious eye irritation. |
| H351 | Suspected of causing cancer. |
| H361d | Suspected of damaging the unborn child. |
| H372 | Causes damage to organs through prolonged or repeated exposure. |

| Precautionary statements | |
|--------------------------|--|
| P201 | Obtain special instructions before use. |
| P280 | Wear protective gloves/protective clothing/eye protection/face protection. |
| P302+P352 | IF ON SKIN: Wash with plenty of water/... |
| P308+P311 | IF exposed or concerned: Call a POISON CENTER/doctor/... |

For use in industrial installations only.

2.3 Other hazards

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.



SECTION 3: Composition / information on ingredients

3.1 Substances

not applicable

3.2 Mixtures

Hazardous ingredients Classification according to Regulation (EC) No 1272/2008 [CLP]

| Substance name | Concentration | Identifier | Hazard classes and hazard categories |
|------------------|---------------|--|--|
| Chloroform | > 99% | CAS No.: 67-66-3 EC No.: 200-663-8 REACH No.: 01-2119486657-20-XXXX | Acute Tox. 3 - H331 Acute Tox. 4 - H302 Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 Carc. 2 - H351 Repr. 2 - H361d STOT RE 1 - H372 |
| Ethanol absolute | < 1% | CAS No.: 64-17-5 EC No.: 200-578-6 REACH No.: 01-2119457610-43-XXXX | Flam. Liq. 2 - H225 Eye Irrit. 2 - H319 |

SECTION 4: First aid measures

4.1 General information

If exposed or if you feel unwell: Call a POISON CENTRE or doctor/physician. If unconscious but breathing normally, place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

After inhalation

Call a POISON CENTRE/doctor. Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

In case of ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

Self-protection of the first aider

First aider: Pay attention to self-protection!

4.2 Most important symptoms and effects, both acute and delayed

no data available

4.3 Indication of any immediate medical attention and special treatment needed

no data available

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

The product itself does not burn.

Co-ordinate fire-fighting measures to the fire surroundings.

Extinguishing media which must not be used for safety reasons

no restriction

5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated:

Pyrolysis products, toxic

5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives.

Special protective equipment for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use water spray jet to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety.

6.2 Environmental precautions

Discharge into the environment must be avoided.

6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Collect in closed and suitable containers for disposal.

6.4 Additional information

Clear spills immediately.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

All work processes must always be designed so that the following is as low as possible:

Inhalation

skin contact

Eye contact

Use extractor hood (laboratory).

If handled uncovered, arrangements with local exhaust ventilation have to be used.

If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: 15-25°C

Storage class: 10-13

Keep container tightly closed and in a well-ventilated place. Keep/Store only in original container.

7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

| Ingredient (Designation) | Regulatory information | Country | Limit value type (country of origin) | Limit value | Remark |
|-----------------------------|---------------------------|---------|---|------------------------------|--------|
| Chloroform | 2000/39/EC | EU | LTV | 10 mg/m ³ - 2 ppm | |
| Chloroform | Gestis | EU | LTV | 10 mg/m ³ - 2 ppm | |

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

8.2.2 Personal protection equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn.

Eye/face protection

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

Recommendation: VWR 111-0432

Skin protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms EN ISO 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.

By short-term hand contact

| | |
|----------------------------------|---|
| Suitable material: | Butyl caoutchouc (butyl rubber)/FKM (fluoro rubber) |
| Thickness of the glove material: | 0,70 mm |
| Breakthrough time:: | 120-240 min |
| Recommended glove articles: | VWR 112-3819 |

By long-term hand contact

| | |
|----------------------------------|-------------------------|
| Suitable material: | PVA (Polyvinyl alcohol) |
| Thickness of the glove material: | - |
| Breakthrough time:: | > 480 min |
| Recommended glove articles: | VWR 112-0269 |

Respiratory protection

Respiratory protection necessary at: aerosol or mist formation

| | |
|--|---|
| Suitable respiratory protection apparatus: | Full-/half-/quarter-face masks (DIN EN 136/140) |
| Recommendation: | VWR 111-0206 |
| Suitable material: | A2 |
| Recommendation: | VWR 111-0053 |

Additional information

Wash hands before breaks and after work. Avoid contact with eyes and skin. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

8.2.3 *Environmental exposure controls* no data available

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

| | |
|----------------------|-------------------|
| (a) Appearance | |
| Physical state: | liquid |
| Colour: | colourless |
| (b) Odour: | no data available |
| (c) Odour threshold: | no data available |

Safety relevant basic data

| | |
|--|-----------------------------------|
| (d) pH: | no data available |
| (e) Melting point/freezing point: | -63 °C |
| (f) Initial boiling point and boiling range: | 61.7 °C (1013 hPa) |
| (g) Flash point: | no data available |
| (h) Evaporation rate: | no data available |
| (i) Flammability (solid, gas): | not applicable |
| (j) Flammability or explosive limits | |
| Lower explosion limit: | no data available |
| Upper explosion limit: | no data available |
| (k) Vapour pressure: | 210 hPa (20 °C) |
| (l) Vapour density: | 4.12 (20 °C) |
| (m) Relative density: | 1.48320 g/cm ³ (20 °C) |
| (n) Solubility(ies) | |
| Water solubility: | no data available |
| Soluble (g/L) in Ethanol: | no data available |
| (o) Partition coefficient: n-octanol/water: | 1.97 (20 °C) |
| (p) Auto-ignition temperature: | 982 °C |
| (q) Decomposition temperature: | no data available |
| (r) Viscosity | |
| Kinematic viscosity: | no data available |
| Dynamic viscosity: | 0.56 mPa*s (20 °C) |
| (s) Explosive properties: | not applicable |
| (t) Oxidising properties: | not applicable |

9.2 Other information

| | |
|------------------------|-------------------|
| Bulk density: | no data available |
| Refraction index: | no data available |
| Dissociation constant: | no data available |
| Surface tension: | no data available |
| Henry's Law Constant: | no data available |

SECTION 10: Stability and reactivity

10.1 Reactivity

no data available

10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

no data available

10.6 Hazardous decomposition products

no data available

10.7 Additional information

no data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:

Chloroform - LD50: > 695 mg/kg - Rat - (RTECS)

Chloroform - LDLo: > 2514 mg/kg - Human - (RTECS)

Ethanol absolute - LD50: > 6200 mg/kg - Rat - (Merck KGaA)

Acute dermal toxicity:

Chloroform - LD50: > 20 g/kg - Rabbit - (National Library of Medicine ChemID Plus (NLM CIP))

Ethanol absolute - LD50: < 20000 mg/kg - Rabbit - (CHP)

Acute inhalation toxicity:

Chloroform - LC50: 47702 mg/m³ - Rat - (National Library of Medicine ChemID Plus (NLM CIP))

Ethanol absolute - LC50: < 8000 mg/l (4h) - Rat - (CHP)

Irritant and corrosive effects

Primary irritation to the skin:

Causes skin irritation.

Irritation to eyes:

Causes serious eye irritation.

Irritation to respiratory tract:

not applicable

Respiratory or skin sensitisation

In case of skin contact: not sensitising

After inhalation: not sensitising

STOT-single exposure

not applicable

STOT-repeated exposure

Causes damage to organs through prolonged or repeated exposure.

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Carcinogenicity

Suspected of causing cancer.

Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.

Reproductive toxicity

Suspected of damaging the unborn child.

Aspiration hazard

not applicable

Other adverse effects

no data available

Additional information

no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Fish toxicity:

Chloroform - LC50: 28 mg/l (96 h) - Pearson, C.R., and G. McConnell 1975. Chlorinated C1 and C2 Hydrocarbons in the Marine Environment. Proc.R.Soc.Lond.B Biol.Sci. 189:305-332

Ethanol absolute - LC50: 11000 mg/l (96 h) - Bengtsson, B.E., L. Renberg, and M. Tarkpea 1984. Molecular Structure and Aquatic Toxicity - an Example with C1-C13 Aliphatic Alcohols. Chemosphere 13(5/6):613-622

Daphnia toxicity:

Chloroform - LC50: 66.8 mg/l (48 h) - Gersich, F.M., F.A. Blanchard, S.L. Applegath, and C.N. Park 1986. The Precision of Daphnid (Daphnia magna Straus, 1820) Static Acute Toxicity Tests. Arch.Environ.Contam.Toxicol. 15(6):741-749

Ethanol absolute - LC50: 9280 mg/l (48 h) - Takahashi, I.T., U.M. Cowgill, and P.G. Murphy 1987. Comparison of Ethanol Toxicity to Daphnia magna and Ceriodaphnia dubia Tested at Two Different Temperatures: Static Acute Toxicity Test Results. Bull.Environ.Contam.Toxicol. 39(2):229-236

Ethanol absolute - EC50: 9950 mg/l (48 h) - Barera, Y., and W.J. Adams 1983. Resolving Some Practical Questions About Daphnia Acute Toxicity Tests. In: W.E.Bishop (Ed.), Aquatic Toxicology and Hazard Assessment, 6th Symposium, ASTM STP 802, Philadelphia, PA :509-518

Algae toxicity:

no data available

Bacteria toxicity:

no data available

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: 1.97 (20 °C)

12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6 Other adverse effects

no data available

SECTION 13: Disposal considerations**13.1 Waste treatment methods****Appropriate disposal / Product**

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

Additional information

no data available

SECTION 14: Transport information

Land transport (ADR/RID)

| | | |
|------|--|--|
| 14.1 | UN-No.: | 1888 |
| 14.2 | Proper Shipping Name: | CHLOROFORM |
| 14.3 | Class(es): | 6.1 |
| | Classification code: | T1 |
| | Hazard label(s): | 6.1 |
| 14.4 | Packing group: | III |
| 14.5 | Environmental hazards: | No |
| 14.6 | Special precautions for user: | |
| | Hazard identification number (Kemler No.): | 60 |
| | tunnel restriction code: | E |
| | | (Passage forbidden through tunnels of category E.) |

Sea transport (IMDG)

| | | |
|------|--|------------|
| 14.1 | UN-No.: | 1888 |
| 14.2 | Proper Shipping Name: | CHLOROFORM |
| 14.3 | Class(es): | 6.1 |
| | Classification code: | |
| | Hazard label(s): | 6.1 |
| 14.4 | Packing group: | III |
| 14.5 | Environmental hazards: | No |
| | Marine pollutant: | No |
| 14.6 | Special precautions for user: | |
| | Segregation group: | 10 |
| | EmS-No. | F-A S-A |
| 14.7 | Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code | |
| | not relevant | |

Air transport (ICAO-TI / IATA-DGR)

| | | |
|------|-------------------------------|------------|
| 14.1 | UN-No.: | 1888 |
| 14.2 | Proper Shipping Name: | CHLOROFORM |
| 14.3 | Class(es): | 6.1 |
| | Classification code: | |
| | Hazard label(s): | 6.1 |
| 14.4 | Packing group: | III |
| 14.5 | Special precautions for user: | |



SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

- Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC (Text with EEA relevance)
- Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 (Text with EEA relevance)
- Commission Regulation (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (Text with EEA relevance)
- Commission Regulation (EU) 2015/830 of 28 May 2015 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)

Use restriction according to REACH annex XVII:

- Number: 32 (Chloroform)

National regulations

no data available

Water hazard class: no data available

15.2 Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.



SECTION 16: Other information

Abbreviations and acronyms

H225 - Highly flammable liquid and vapour.

H302 - Harmful if swallowed.

H315 - Causes skin irritation.

H319 - Causes serious eye irritation.

H331 - Toxic if inhaled.

H351 - Suspected of causing cancer.

H361d - Suspected of damaging the unborn child.

H372 - Causes damage to organs through prolonged or repeated exposure.

ACGIH - American Conference of Governmental Industrial Hygienists

ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road

AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)

CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures

DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)

Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)

IATA-DGR - International Air Transport Association-Dangerous Goods Regulations

ICAO-TI - International Civil Aviation Organization-Technical Instructions

IMDG - International Maritime Code for Dangerous Goods

LTV - Long Term Value

NIOSH - National Institute for Occupational Safety and Health

OSHA - Occupational Safety & Health Administration

PBT - Persistent, Bioaccumulative and Toxic

RID - Regulation concerning the International Carriage of Dangerous Goods by Rail

STV - Short Term Value

SVHC - Substances of Very High Concern

vPvB - very Persistent, very Bioaccumulative

Training advice: Provide adequate information, instruction and training for operators.



Classification according to Regulation (EC) No 1272/2008 [CLP] - Classification procedure

| Hazard statements | Hazard classes and hazard categories | Classification procedure |
|-------------------|--------------------------------------|--------------------------|
| H331 | Acute Tox. 3 | Calculation method. |
| H302 | Acute Tox. 4 | Calculation method. |
| H315 | Skin Irrit. 2 | Calculation method. |
| H319 | Eye Irrit. 2 | Calculation method. |
| H351 | Carc. 2 | Calculation method. |
| H361d | Repr. 2 | Calculation method. |
| H372 | STOT RE 1 | Calculation method. |

Additional information

Indication of changes general update

If you need an explanation of the change, contact the supplier. (SDS@avantorsciences.com)

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.