



# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH)

Revision date: 24.07.2020 Version: 7.1 Print date: 24.07.2020

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

Trade name/designation: Toluene AnalaR NORMAPUR®

Product No.: 10284
CAS No.: 108-88-3
Index No.: 601-021-00-3

REACH No.: 01-2119471310-51-XXXX

Other means of identification: Methylbenzene, Phenylmethane, Ramipril Impurity G (EP)

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses: General chemical reagent

### 1.3 Details of the supplier of the safety data sheet

# **United Kingdom**

#### VWR International Ltd.

Street Hunter Boulevard, Magna Park

Postal code/City Lutterworth, LE17 4XN

 Telephone
 0800 22 33 44

 Telefax:
 01455 55 85 86

 E-mail (competent person)
 SDS@vwr.com

### 1.4 Emergency phone number

Telephone +44 (0) 1270 502894 (CareChem24)





# SECTION 2: Hazard identification

#### 2.1 Classification of the substance or mixture

#### 2.1.1 Classification according to Regulation (EC) No 1272/2008 [CLP]

Hazard classes and hazard categories	Hazard statements
Flammable liquid, category 2	H225
Aspiration hazard, category 1	H304
Skin irritation, category 2	H315
Reproductive toxicity, category 2	H361d
Specific target organ toxicity (repeated exposure), category 2	H373
Specific target organ toxicity (single exposure), category 3, narcotic effect	H336

#### 2.2 **Label elements**

#### Labelling according to Regulation (EC) No. 1272/2008 [CLP] 2.2.1

### **Hazard pictograms**



Signal word: Danger

Hazard statements	
H225	Highly flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H361d	Suspected of damaging the unborn child.
H373	May cause damage to organs through prolonged or repeated exposure.
H336	May cause drowsiness or dizziness.





Precautionary	
statements	
P201	Obtain special instructions before use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P243	Take precautionary measures against static discharge.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P301+P330+P331	IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P302+P352	IF ON SKIN: Wash with plenty of water/
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P308+P310	IF exposed or concerned: Immediately call a POISON CENTER/doctor.
P403+P235	Store in a well-ventilated place. Keep cool.

#### 2.3 Other hazards

This substance does not meet the PBT/vPvB criteria of REACH, Annex XIII.

## SECTION 3: Composition / information on ingredients

#### 3.1 Substances

Substance name Toluene Molecular formula  $C_6H_5CH_3$  Molecular weight 92.14 g/mol CAS No. 108-88-3

REACH registration No. 01-2119471310-51-XXXX

Index No. 601-021-00-3

### **SECTION 4: First aid measures**

#### 4.1 General information

IF exposed: Immediately call a POISON CENTRE/doctor. If unconscious but breathing normally, place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

### After inhalation

Immediately call a POISON CENTRE/doctor. Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

### In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

#### After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.





### In case of ingestion

Immediately call a POISON CENTRE/doctor. Do NOT induce vomiting. Rinse mouth thoroughly with water. Give nothing to eat or drink.

#### Self-protection of the first aider

First aider: Pay attention to self-protection!

#### 4.2 Most important symptoms and effects, both acute and delayed

no data available

### 4.3 Indication of any immediate medical attention and special treatment needed

no data available

### **SECTION 5: Firefighting measures**

### 5.1 Extinguishing media

#### Suitable extinguishing media

Water spray ABC-powder Carbon dioxide (CO2) Nitrogen

#### Extinguishing media which must not be used for safety reasons

no restriction

### 5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated: Carbon monoxide Carbon dioxide (CO2)

### 5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives.

Special protective equipment for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

#### **Additional information**

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen.

Use water spray jet to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

### **SECTION 6: Accidental release measures**

#### 6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety.

### **6.2 Environmental precautions**

Discharge into the environment must be avoided.





#### 6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Collect in closed and suitable containers for disposal.

#### 6.4 Additional information

Clear spills immediately.

### **SECTION 7: Handling and storage**

### 7.1 Precautions for safe handling

Avoid:

Inhalation

Avoid contact with eyes and skin.

Use extractor hood (laboratory).

If handled uncovered, arrangements with local exhaust ventilation have to be used.

If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

Keep away from sources of ignition - No smoking.

Usual measures for fire prevention.

Take precautionary measures against static discharges.

#### 7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: 15-25°C

Storage class: 3

Keep container tightly closed and in a well-ventilated place. Keep/Store away from combustible materials.

#### 7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

### SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

### 8.2 Exposure controls

### 8.2.1 Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

#### 8.2.2 Personal protection equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn.

Eye/face protection

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

Recommendation: VWR 111-0432

Skin protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms EN ISO 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.





### By short-term hand contact

Suitable material: NBR (Nitrile rubber)

Thickness of the glove material: 0,425 mm Breakthrough time:: 30 min

Recommended glove articles: VWR 112-0971

#### By long-term hand contact

Suitable material: PE (polyethylene)

Thickness of the glove material:

Breakthrough time:: > 480 min
Recommended glove articles: VWR 112-1009

### Respiratory protection

Respiratory protection necessary at: aerosol or mist formation

Suitable respiratory protection apparatus: Full-/half-/quarter-face masks (DIN EN 136/140)

Recommendation: VWR 111-0206
Suitable material: ABEK2P3
Recommendation: VWR 111-0059

### Additional information

Wash hands before breaks and after work. Avoid contact with eyes and skin. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

### **8.2.3** Environmental exposure controls

no data available





### **SECTION 9: Physical and chemical properties**

### 9.1 Information on basic physical and chemical properties

(a) Appearance

Physical state: liquid
Colour: colourless

(b) Odour: no data available
(c) Odour threshold: no data available

### Safety relevant basic data

(d) pH: no data available

(e) Melting point/freezing point: -95 °C

(f) Initial boiling point and boiling range: 110.6 °C (1013 hPa)

(g) Flash point: 4 °C

(h) Evaporation rate: no data available

(i) Flammability (solid, gas): Highly flammable liquid and vapour.

no data available

(j) Flammability or explosive limits

(q) Decomposition temperature:

Lower explosion limit: 1.2 % (v/v)
Upper explosion limit: 8 % (v/v)
(k) Vapour pressure: 29 hPa (20 °C)
(l) Vapour density: 3.14 (20 °C)

(m) Relative density: 0.867 g/cm³ (20 °C)

(n) Solubility(ies)

Water solubility: 520 mg/l (20 °C)
Soluble (g/L) in Ethanol: no data available

(o) Partition coefficient: n-octanol/water: 2.73 (20 °C)

(p) Auto-ignition temperature: 535 °C (DIN 51794)

(r) Viscosity

Kinematic viscosity: no data available
Dynamic viscosity: 0.6 mPa\*s (20 °C)
(s) Explosive properties: not applicable
(t) Oxidising properties: not applicable

### 9.2 Other information

Bulk density: no data available
Refraction index: 1.4967 (589 nm; 20 °C)
Dissociation constant: no data available
Surface tension: no data available
Henry's Law Constant: no data available

### SECTION 10: Stability and reactivity

#### 10.1 Reactivity

no data available





### 10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

### 10.3 Possibility of hazardous reactions

no data available

#### 10.4 Conditions to avoid

no data available

### 10.5 Incompatible materials

no data available

### 10.6 Hazardous decomposition products

no data available

#### 10.7 Additional information

no data available

# SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### **Acute effects**

Acute oral toxicity:

LD50: > 636 mg/kg - Rat - (IUCLID)

Acute dermal toxicity:

LD50: > 12124 mg/kg - Rabbit - (IUCLID)

Acute inhalation toxicity:

LC50: 12.5 mg/l - Rat - (Japan GHS Basis for Classification Data)

#### Irritant and corrosive effects

Primary irritation to the skin:

Causes skin irritation.

Irritation to eyes:

not applicable

Irritation to respiratory tract:

not applicable





#### Respiratory or skin sensitisation

In case of skin contact: not sensitising After inhalation: not sensitising

#### STOT-single exposure

May cause drowsiness or dizziness.

#### STOT-repeated exposure

May cause damage to organs through prolonged or repeated exposure.

# CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

#### Carcinogenicity

No indication of human carcinogenicity.

#### Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.

#### Reproductive toxicity

Suspected of damaging the unborn child.

#### **Aspiration hazard**

May be fatal if swallowed and enters airways.

#### Other adverse effects

no data available

#### **Additional information**

no data available

### **SECTION 12: Ecological information**

### 12.1 Ecotoxicity

#### Fish toxicity:

LC50: 31.7 mg/l (96 h) - Geiger, D.L., L.T. Brooke, and D.J. Call 1990. Acute Toxicities of Organic Chemicals to Fathead Minnows (Pimephales promelas), Volume 5. Ctr.for Lake Superior Environ.Stud., Univ.of Wisconsin-Superior, Superior, WI:332 p.

#### Daphnia toxicity:

EC50: 9.24 mg/l (48 h) - MacLean, M.M., and K.G. Doe 1989. The Comparative Toxicity of Crude and Refined Oils to Daphnia magna and Artemia. Environment Canada, EE-111, Dartmouth, Nova Scotia :64 p

LC50: 92 mg/l (48 h) - MacLean, M.M., and K.G. Doe 1989. The Comparative Toxicity of Crude and Refined Oils to Daphnia magna and Artemia. Environment Canada, EE-111, Dartmouth, Nova Scotia :64 p.

### Algae toxicity:

EC50: 12.5 mg/l (72 h) - Galassi, S., M. Mingazzini, L. Vigano, D. Cesareo, and M.L.Tosato 1988. Approaches to Modeling Toxic Responses of Aquatic Organisms to Aromatic Hydrocarbons. Ecotoxicol.Environ.Saf. 16(2):158-169

#### **Bacteria toxicity:**

no data available





### 12.2 Persistence and degradability

no data available

#### 12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: 2.73 (20 °C)

### 12.4 Mobility in soil:

no data available

### 12.5 Results of PBT/vPvB assessment

This substance does not meet the PBT/vPvB criteria of REACH, Annex XIII.

#### 12.6 Other adverse effects

no data available

# SECTION 13: Disposal considerations

#### 13.1 Waste treatment methods

#### Appropriate disposal / Product

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: 070104

#### Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

### **Additional information**

no data available

### **SECTION 14: Transport information**

#### Land transport (ADR/RID)

14.1	UN-No.:	1294
14.2	Proper Shipping Name:	TOLUENE
14.3	Class(es):	3
	Classification code:	F1
	Hazard label(s):	3
14.4	Packing group:	II
14.5	Environmental hazards:	No
14.6	Special precautions for user:	

Hazard identification number (Kemler No.): 33 tunnel restriction code: D/E

(Passage forbidden through tunnels of category D when carried in bulk or in tanks. Passage forbidden through tunnels of category E.)





### Sea transport (IMDG)

14.1	UN-No.:	1294
14.2	Proper Shipping Name:	TOLUENE
14.3	Class(es):	3
	Classification code:	
	Hazard label(s):	3
14.4	Packing group:	II
14.5	Environmental hazards:	No
	Marine pollutant:	No
14.6	Special precautions for user:	
	Segregation group:	-
	EmS-No.	F-E S-D
14.7	Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code not relevant	

# Air transport (ICAO-TI / IATA-DGR)

14.1	UN-No.:	1294
14.2	Proper Shipping Name:	TOLUENE
14.3	Class(es):	3
	Classification code:	
	Hazard label(s):	3
14.4	Packing group:	II
14.5	Special precautions for user:	





### **SECTION 15: Regulatory information**

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### **EU** legislation

- Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC (Text with EEA relevance)
- Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 (Text with EEA relevance)
- Commission Regulation (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (Text with EEA relevance)
- Commission Regulation (EU) 2015/830 of 28 May 2015 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)

Use restriction according to REACH annex XVII, no.: 48

#### **National regulations**

no data available

Water hazard class: hazardous to water (WGK 2)

#### 15.2 Chemical Safety Assessment

For this substance a chemical safety assessment has not been carried out.





### **SECTION 16: Other information**

#### Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygiensts

ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road

AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)

CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures

DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)

Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)

IATA-DGR - International Air Transport Association-Dangerous Goods Regulations

ICAO-TI - International Civil Aviation Organization-Technical Instructions

IMDG - International Maritime Code for Dangerous Goods

LTV - Long Term Value

NIOSH - National Institute for Occupational Safety and Health

OSHA - Occupational Safety & Health Administration

PBT - Persistent, Bioaccumulative and Toxic

RID - Regulation concerning the International Carriage of Dangerous Goods by Rail

STV - Short Term Value

SVHC - Substances of Very High Concern

vPvB - very Persistent, very Bioaccumulative

Training advice: Provide adequate information, instruction and training for operators.

#### **Additional information**

Indication of changes general update

If you need an explanation of the change, contact the supplier.

(SDS@avantorsciences.com)

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.