



1.0 M Tris HCl pH 7.2 - MB-001

Code: MB-001

Size: 1 L

Product Description: 1.0 M Tris HCl pH 7.2 - MB-001

PhysicalState: Liquid (sterile filtered)

Label	Unconjugated
Buffer	See application note.
Stabilizer	None
Preservative	None
Storage Condition	Store container at room temperature (18° to 26° C) prior to opening. If desired, the solution may be stored at 4° C or less. Some salts may precipitate out of solution at lower temperature. Allow buffer to equilibrate to room temperature (18° to 26° C) to restore solubility of some salts.
Synonyms	Tris solution, THAM, tris(hydroxymethyl)aminomethane
Application Note	Suitable for molecular immunology, molecular biology and nucleic acid methodologies, when applicable. Visit our newly expanded web site at www.rockland-inc.com for methods using this and other buffers. This product is a concentrated stock solution and should be diluted appropriately with distilled, deionized water or equivalent to its final working concentration. This buffer consists of 1.0 M Tris HCl at pH 7.2. Meticulously prepared using ultra pure reagents dissolved in highly polished pharmaceutical grade deionized water.
Background	Tris solution is an abbreviation of the organic compound known as tris(hydroxymethyl)aminomethane. Tris is extensively used in biochemistry and molecular biology. In biochemistry, Tris is widely used as a component of buffer solutions, such as in TAE and TBE buffer, especially for solutions of nucleic acids.
Purity And Specificity	This product was aseptically filtered through a Millipore 0.22 micron filter into clean, pre-sterilized containers. The product was tested on trypticase soy agar for 24 hours, 48 hours and 72 hours and was found to be negative for bacteria.
Expiration	Expiration date is six (6) months from date of opening.

Related Products

610-4302	Anti-MOUSE IgG (H&L) (RABBIT) Antibody Peroxidase Conjugated - 610-4302
611-1302	Anti-RABBIT IgG (H&L) (GOAT) Antibody Peroxidase Conjugated - 611-1302
B304	NORMAL GOAT SERUM (NGS) - B304

Related Links

Images

1	This product is a concentrated stock solution and should be diluted appropriately with distilled, deionized water or equivalent to its final working concentration. This buffer consists of 1.0 M Tris HCl at pH 7.2. Meticulously prepared using ultra pure reagents dissolved in highly polished pharmaceutical grade deionized water.
---	--



Disclaimer

This product is for research use only and is not intended for therapeutic or diagnostic applications. Please contact a technical service representative for more information. All products of animal origin manufactured by Rockland Immunochemicals are derived from starting materials of North American origin. Collection was performed in United States Department of Agriculture (USDA) inspected facilities and all materials have been inspected and certified to be free of disease and suitable for exportation. All properties listed are typical characteristics and are not specifications. All suggestions and data are offered in good faith but without guarantee as conditions and methods of use of our products are beyond our control. All claims must be made within 30 days following the date of delivery. The prospective user must determine the suitability of our materials before adopting them on a commercial scale. Suggested uses of our products are not recommendations to use our products in violation of any patent or as a license under any patent of Rockland Immunochemicals, Inc. If you require a commercial license to use this material and do not have one, then return this material, unopened to: Rockland Inc., P.O. BOX 326, Gilbertsville, Pennsylvania, USA.