



## Product Specifications sheet

# VWR Standard Line Tissue Culture dish Ø 100 mm, with gripping ring.

Cat. No.	Diameter (mm)	Dish size Ø ext. x high (mm)	Approx.culture area (cm <sup>2</sup> )	Unit / Inner bag	Pack size
734-2321	87.8	95.6 x 22.0	60.8	10	300



**Intended uses:** Cell culture  
Suitable for microbiology

**Material:** 100% USP VI crystal virgin polystyrene  
Optical Clear

**Sterilisation:** by Gamma irradiation SAL 10<sup>-6</sup>

**Pyrogene:** certified non-pyrogenic

**Shelf life:** 3 years after month of production

**Product Characteristics:** Produced in 100,000 grade cleanroom environment  
Manufactured under a Quality Management System as per ISO9001:2008  
Uniform well volume ensures equal growth surface area  
Raised rims on wells with uniform rings on the lid to reduce evaporation  
Single position lid reduces the risks of contamination and misplay of handling  
Wells with alphanumeric code for easy identification  
Temperature range: -20° C to +50° C  
Autoclavability: No

**Packaging:** Packed in zip resealable self-standing bags of 10; case of 300 dishes

**Disclaimer:** VWRwants to state that these specifications can only be regarded as general information and will not discharge the user from his obligation to ensure the product is suitable for the intended use - If there's any doubt, ask us.