



Product Specification Sheet

VWR TEST TUBES WITHOUT RIM

VWR International certifies that the specified products meet all VWR specifications and quality criteria for release. The products comply in every respect with the relevant particular specifications, drawings, relevant standards and regulations in force.

VWR International certifie que les produits mentionnés respectent toutes les spécifications et critères de qualité VWR. Les produits satisfont aux spécifications particulières, aux plans, aux normes et règlements en vigueur s'y rapportant.

VWR International bestätigt hiermit, daß die angegebenen Produkte alle VWR Spezifikationen und Qualitätskriterien zur Freigabe erfüllen. Die Produkte entsprechen in jeder Hinsicht den maßgeblichen Spezifikationen, den Zeichnungen sowie den relevanten Normen und gültigen Vorschriften.

Cat. No.	Length (mm)	Wall thickness	Ø ext.	Pk
212-0027	75	0.8 - 1.0 mm	10 mm	100
212-0028	75	0.8 - 1.0 mm	12 mm	100
212-0029	100	0.8 - 1.0 mm	10 mm	100
212-0030	100	0.8 - 1.0 mm	12 mm	100
212-0031	160	0.8 - 1.0 mm	16 mm	100
212-0032	180	0.8 - 1.0 mm	18 mm	100
212-0318	130	0.9 - 1.0 mm	14 mm	100
212-0319	130	1.1 - 1.2 mm	16 mm	100
212-0320	150	1.1 - 1.2 mm	20 mm	100
212-0321	180	1.1 - 1.2 mm	20 mm	100
212-0322	150	1.1 - 1.2 mm	25 mm	50
212-0323	200	1.1 - 1.2 mm	25 mm	50
212-0324	200	1.1 - 1.2 mm	30 mm	50

Material : Borosilicate glass, grade 3.3

Other Characteristics:

- High chemical resistance
- High temperature resistance
- Minimal thermal expansion

Disclaimer: VWR wants to state that these specifications can only be regarded as general information and will not discharge the user from his obligation to ensure the product is suitable for the intended use - If there is any doubt ask us.

Date of issue: **August 2012**

VWR International bvba/sprl, Researchpark Haasrode 2020, Geldenaaksebaan 464, 3001 Leuven, Belgium

<http://www.vwr.com>



Version: 2.0