

Datasheet

RCOR1 monoclonal antibody, clone S72-8 (ATTO 390)

Catalog Number: MAB11927

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against partial recombinant RCOR1.

Clone Name: S72-8

Immunogen: Recombinant fusion protein corresponding to amino acids of 109-293, including ELM2 and SANT domains, of human RCOR1.

Host: Mouse

Reactivity: Human, Mouse, Rat

Applications: ICC, IHC, IP, WB

(See our web site product page for detailed applications information)

Protocols: See our web site at <http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Conjugation: ATTO 390

Purification: Protein G Purification

Isotype: IgG1

Recommend Usage: Western Blot (1 ug/mL)

Immunocytochemistry (0.1-1 ug/mL)

Immunohistochemistry (0.1-1 ug/mL)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.4 (50% glycerol, 0.09% sodium azide)

Storage Instruction: Store at 4°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 23186

Gene Symbol: RCOR1

Gene Alias: COREST, KIAA0071, RCOR

Gene Summary: The RCOR gene encodes a functional corepressor required for regulation of neural-specific gene expression.[supplied by OMIM]